



CitySwan Wall – stylish and discreet

CitySwan Wall

Being part of the CitySwan family designed by Danish architects Bjarne Schläger and Morten Weeke Borup, the CitySwan Wall luminaire has a stylish, discreet, graceful appearance. The luminaire provides downward functional surface light from high-performance LEDs with incredibly low energy consumption, and can also be used as an up-light under e.g. baldachins or archways. It is made of dark grey die-cast aluminum, and the housing has a characteristic ellipsoid shape familiar from the CitySwan road luminaire. CitySwan Wall comes with a choice of three different optical covers: a transparent flat cover for the slickest design, a convex transparent cover for a more elongated light distribution and a flat, opal cover for optimum uniformity. Nominated for the German "Designpreis" in 2009; Danish Design Award 2010/2011. Design: Bjarne Schläger, light + architecture, and Morten Weeke Borup, GHB Landskabsarkitekter A/S.

Fordeler

- Stylish and discreet
- Choice of three different optical covers
- Incredibly low energy consumption

Funksjoner

- Ellipsoid housing
- High-performance LEDs
- Downward functional surface light

Søknad

- Urban environments

Versions



Godkjenning og bruk

Mek. støt, beskyttelseskode	IK10
-----------------------------	------

Kontroller og dimming

Dimmbar	No
---------	----

Generell informasjon

CE-merke	CE mark
Fargevalg	Black Noir 200 Sablé
Lyskildefarge	740 nøytralhvit
Driver inkludert	Ja
lyskildeseriekode	LED-HB
Lyskilde kan erstattes	No
Antall forkoblingsenheter	1 unit
Antall lyskilder	1
Produktseriekode	BWP445

Innledende ytelse (i samsvar med IEC)

Oppr. Korr. Fargetemperatur	4000 K
-----------------------------	--------

Generell informasjon

Order Code	Full Product Name	Optisk deksel-/		
		linsetype	Test av glødetråd	Optikktype
09633900	BWP445 LED/740 II 230V PCC	PCC	Temperatur 850 °C, varighet 5 sek	-
09634600	BWP445 LED/740 II 230V FG BK-200	FG	-	-

