



# Sensored Spiral shaped lamp with high performance bright light, bringing the beauty of light outside

## Tornado T2 Automatic

Energy-saving lamp with built-in light sensor, design ideally for areas where light is required at night. It switches on automatically at dusk and turns off at dawn. The automatic light sensor is simple to use, Tornado has high performance bright light and fits everywhere due to its further compact design.

### Benefits

- Provide maximum convenience in simple usage and safety
- Automatic light sensor, ideal for areas outside a home where light is required at night, automatically turn on at dusk and off at dawn
- Save your money with long life-time and high energy efficiency

### Features

- Long-Life and Energy Saving alternative to Incandescent lamps
- Automatically switches on when it is dark and switches off in daylight

### Application

- Suitable for outdoor applications like gardens, which require the light to come on automatically when the surroundings become dark
- Not suitable for use with dimmers or electronic gear


# Tornado T2 Automatic

## Versions



15W, E27 Automatic

## Dimensional drawing



Product	D (max)	C (max)	F (max)
Tornado T2 Autom 15W WW E27 1PF/6	51.0 mm	107.5 mm	42.5 mm

