



# Metronomis – bespoke solutions

## Metronomis Bordeaux

Metronomis is a family of ten highly distinctive luminaires and dedicated supports (masts and brackets), which can be used with a wide variety of optics to provide architects and lighting designers with the total solution needed to create a unified, consistent lighting design that still reflects the differences in urban culture and history. In its daytime appearance, Metronomis integrates harmoniously with any street scene, while its night-time appearance is both functional – guiding people and traffic safely through the city – and decorative, creating a pleasant ambience in city squares and pedestrian precincts. As the current range is based on conventional light sources, four highly innovative, LED-dedicated designs have been developed, echoing the original silhouette but retaining flexibility and modularity as key characteristics. The Metronomis LED range offers a number of new ways to personalize your urban projects. Please check out the Metronomis LED luminaire variants.

### Benefits

- Total solution with both luminaires and supports forming part of a complete, integrated concept
- Huge range of optical elements and light sources makes it possible to create different atmospheres within the city using a single, perfectly coordinated system
- Dedicated masts and brackets match the style of the luminaires

### Features

- Wide range of optical elements and light sources
- Five mast designs in steel, aluminum and wood, with heights from 3.5 to 12 m

### Application

- Urban and architectural areas
- Commercial and business centers

## Specifications

<b>Type</b>	CDS592/594	<b>Optical cover</b>	Transparent bowl and cover (TT)
<b>Light source</b>	HID:		Opal bowl and transparent cover (OT)
	- 1 x MASTER CosmoWhite CPO-TW / PGZ12 / 45, 60, 90, 140 W		Transparent bowl and opal cover (TO)
	- 1 x MASTER CityWhite CDO-TT / E27 / 50, 70 W		Opal bowl and cover (OO)
	- 1 x MASTER CityWhite CDO-TT / E40 / 100, 150 W	<b>Ignitor</b>	Semi-parallel (SP)
	- 1 x MASTER Colour CDM-T / G12 / 35, 70, 150 W		Semi-parallel, self-stopping (ST)
	- 1 x MASTER SDW-T / PG12-1 / 50, 100 W		Semi-parallel digital (SND)
	- 1 x SON / E27 / 50, 70 W	<b>Options</b>	Photocell: Minicell (P3)
	- 1 x SON / E40 / 100, 150 W		Filter coil (F)
	- 1 x SON-I / E27 / 50, 70 W	<b>Materials and finishing</b>	Housing: high-pressure, die-cast aluminum
	- 1 x SON-T / E27 / 50, 70 W		Decorative arms: die-cast aluminum
	- 1 x SON-T / E40 / 100, 150 W		Bowls and bowl covers: polycarbonate
	- 1 x SON-T APIA Xtra / 50, 70, 100 W		Refractor and diffuser: polymethylmethacrylic-imide
	Compact fluorescent:		Louvers: high-pressure, die-cast aluminum
	- 1 x MASTER PL-T 4 Pin / GX24q-3 or 4* / 32, 42 W		Reflector assemblies: aluminum
	- *depends on wattage		Adapters: die-cast aluminum
	Induction lamp system:	<b>Color</b>	Dark grey (GR)
	- MASTER QL system / 55 W		Akzo or RAL colors available on request
<b>Lamp included</b>	Yes (K or lamp color 628, 728, 830, 840)	<b>Installation</b>	Side-entry mounting: lateral entry Ø 42 - 60 mm with side-entry adapter
	No		Catenary mounting with catenary adapter
<b>Gear</b>	Electronic, 220 - 240 V / 50 - 60 Hz:		Recommended mounting height: 4 - 6 m
	- Electronic (EB)	<b>Accessories</b>	Adapter for side entry, Ø 42 - 60 mm, ZRP551
<b>Optic (elements)</b>	Louver (LO)		Catenary adapter, ZRP552
	Refractor, prismatic (PR)	<b>Remarks</b>	Compatible with various Metronomis brackets
	Diffuser (DF)	<b>Main applications</b>	Urban and architectural areas, commercial and business centers
	Rotation-symmetrical reflector (S)		
	Road-lighting reflector, asymmetrical (A)		

## Versions



