



Designed for incandescent reflector or halogen replacement in the shape of PAR38

PAR38 Downlighter ESaver

Energy-saving lamp for incandescent reflector replacement or halogen replacement, in professional or home applications

Faydaları

- Increased comfort due to lower heat emission than incandescent or halogen lamps
- Save your money with long life-time and high energy efficiency compare to incandescent lamp
- Lower total cost of ownership than PAR38 incandescent / halogen reflector lamps

Özellikler


- High light intensity in a specific direction (PAR38)
- Longer-life alternative to conventional incandescent or halogen lamps
- Waterproof luminaire
- Not suitable for dimming and electronic devices

Uygulama

- Replacement of incandescent or halogen PAR38 reflector lamps in professional applications (hotels, restaurants, shops, museums, exhibitions)
- Interior applications such as window displays, downlighting; exterior applications such as decorative outdoor lighting (e.g. gardens, statues), floodlighting, facade lighting
- Not suitable for accent lighting, or for use under water unless in a waterproof luminaire

PAR38 Downlighter ESaver

Boyutlu çizim



Product	D (max)	C (max)	F (max)
PAR38 Downl ES 23W WW E27 220-240V 1CH/6	122 mm	140.2 mm	43.5 mm
PAR38 ES 18W WW E27 220-240V 1CH/6	122 mm	140.2 mm	43.5 mm

