



High Color Rendering, High Efficacy, Long Life Lamps

PL-C Cluster 2-Pin Base 15mm Tube

Philips Linear Compact Fluorescent Lamps offer designers, specifiers and end-users new levels of efficiencies and versatility in sizes, configurations and application possibilities. With so many elegant fixtures available to complement their small size, high light output and advanced technology, Philips Energy Advantage lamps are fast becoming the preferred choice when maximum efficiency and sleek design solutions are required.

Benefits

- Enhanced performance – 80% light output between 55° and 127° F*
- Sustainable lighting solution
- Compact quad tube design
- * 80% light output in a base-up position

Features

- Enhanced Performance
- Quad Tube Design
- Dimmable
- 10,000 Hour Rated Average Life*
- Excellent color rendering and broad range of color temperature
- Available in: 20 and 27 watts with 2700 color temperature
- * Average life under specified test conditions with lamps turned off and restarted no more frequently than once every 3 operating hours. Lamp life is appreciably longer if lamps are started less frequently.

Application

- Ideal for downlights and wall washers in general lighting and wall sconces in decorative lighting


PL-C Cluster 2-Pin Base 15mm Tube

Versions



GX32d-2 PL-C

Dimensional drawing



Product
PL-C15mm 28W/827 GX32d-3 1CT

