



High Color Rendering, High Efficacy, Long Life Lamps

PL-C Cluster 2-Pin Base Energy Advantage

Philips Linear Compact Fluorescent Lamps offer designers, specifiers and end-users new levels of efficiencies and versatility in sizes, configurations and application possibilities. With so many elegant fixtures available to complement their small size, high light output and advanced technology, Philips Energy Advantage lamps are fast becoming the preferred choice when maximum efficiency and sleek design solutions are required.

Benefits

- Enhanced performance - 80% light output between 55° and 127 F*
- Sustainable lighting solution.
- Compact quad tube design
- * 80% light output in a base-up position

Features

- Energy savings without changing a ballast
- Excellent color rendering of 82 CRI
- High lamp efficacy
- TCLP compliant* with only 1.4 mg of mercury per lamp-the lowest mercury content in a PL-C lamp in the industry.
- Designed for use with Magnetic Ballasts
- ALTO® Lamp Technology

Application

- Ideal for downlights and wall washers in general lighting; wall sconces in decorative lighting.


PL-C Cluster 2-Pin Base Energy Advantage

Versions



26W, G24d-3, 2P

Dimensional drawing



Product	D (max)	D1 (max)	A (max)	B (max)	C (max)
PL-C 26W/835/XEW/2P/ALTO 21W	27.1 mm	27.1 mm	130.7 mm	149.0 mm	171.4 mm

