



# Product Description

## MASTER PL-C 2 Pin

Energy-saving compact fluorescent lamps. Compact long-arc low-pressure mercury discharge lamp. Envelope consists of 4 parallel narrow fluorescent tubes

### Benefits

- Optimal light performance for short or long operation per switch on
- Long life and sustainable light output

### Features

- 2-pin base with a housing incorporating the special instant starter and capacitor
- Lamp characteristics are influenced by operating conditions and control gear used
- Dimming is not possible

### Application

- Designed for general or supplementary lighting in professional or home environments
- Recessed or surface-mounted downlighters, wall units, table lamps and pendant lamps

### Warnings and Safety

- Use only with electromagnetic control gear
- Lamp light technical and electrical characteristics are influenced by operating conditions, i.e. lamp ambient temperature and operating position
- Dimming is not possible
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.


# MASTER PL-C 2 Pin

## Versions



LPPR PLC2P 18W

## Dimensional drawing



Product	D (max)	D1 (max)	A (max)	B (max)	C (max)
MASTER PL-C 18W/840/2P 1CT/ 5X10BOX	27.1 mm	27.1 mm	109.5 mm	128.0 mm	150.4 mm
MASTER PL-C 18W/865/2P 1CT/ 5X10BOX	27.1 mm	27.1 mm	109.5 mm	128.0 mm	150.4 mm
MASTER PL-C 26W/827/2P 1CT/ 5X10BOX	27.1 mm	27.1 mm	130.5 mm	149.0 mm	171.4 mm
MASTER PL-C 26W/830/2P 1CT/ 5X10BOX	27.1 mm	27.1 mm	130.5 mm	149.0 mm	171.4 mm
MASTER PL-C 26W/840/2P 1CT/ 5X10BOX	27.1 mm	27.1 mm	130.5 mm	149.0 mm	171.4 mm
MASTER PL-C 26W/865/2P 1CT/ 5X10BOX	27.1 mm	27.1 mm	130.5 mm	149.0 mm	171.4 mm

Controls and Dimming	
Dimmable	No
Approval and Application	
Mercury (Hg) Content (Nom)	1.4 mg

## General Information

Order Code	Full Product Name	Cap-Base
927905784001	MASTER PL-C 18W/840/2P 1CT/5X10BOX	G24d-2
927905786502	MASTER PL-C 18W/865/2P 1CT/5X10BOX	G24d-2
927906182701	MASTER PL-C 26W/827/2P 1CT/5X10BOX	G24d-3

Order Code	Full Product Name	Cap-Base
927906183001	MASTER PL-C 26W/830/2P 1CT/5X10BOX	G24d-3
927906184001	MASTER PL-C 26W/840/2P 1CT/5X10BOX	G24d-3
927906186565	MASTER PL-C 26W/865/2P 1CT/5X10BOX	G24d-3

## Light Technical

Order Code	Full Product Name	Color Designation	Correlated Color	Color rendering index (CRI)	Luminous Efficacy (rated)	
			Temperature (Nom)		(Nom)	Luminous Flux
927905784001	MASTER PL-C 18W/840/2P 1CT/5X10BOX	Cool White (CW)	4000 K	82	67 lm/W	1,200 lm
927905786502	MASTER PL-C 18W/865/2P 1CT/5X10BOX	Cool Daylight	6500 K	82	67 lm/W	1,200 lm
927906182701	MASTER PL-C 26W/827/2P 1CT/5X10BOX	Incandescent White	2700 K	82	68 lm/W	1,800 lm

## MASTER PL-C 2 Pin

Order Code	Full Product Name	Color Designation	Correlated Color	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)	Luminous Flux
			Temperature (Nom)			
927906183001	MASTER PL-C 26W/830/2P 1CT/5X10BOX	Warm White (WW)	3000 K	82	68 lm/W	1,800 lm
927906184001	MASTER PL-C 26W/840/2P 1CT/5X10BOX	Cool White (CW)	4000 K	82	68 lm/W	1,800 lm
927906186565	MASTER PL-C 26W/865/2P 1CT/5X10BOX	Cool Daylight	6500 K	80	66 lm/W	1,740 lm

### Operating and Electrical

Order Code	Full Product Name	Lamp Current	Power Consumption
		(Nom)	
927905784001	MASTER PL-C 18W/840/2P 1CT/5X10BOX	0.230 A	17.9 W
927905786502	MASTER PL-C 18W/865/2P 1CT/5X10BOX	0.230 A	17.9 W
927906182701	MASTER PL-C 26W/827/2P 1CT/5X10BOX	0.335 A	26.5 W

Order Code	Full Product Name	Lamp Current	Power Consumption
		(Nom)	
927906183001	MASTER PL-C 26W/830/2P 1CT/5X10BOX	0.335 A	26.5 W
927906184001	MASTER PL-C 26W/840/2P 1CT/5X10BOX	0.335 A	26.5 W
927906186565	MASTER PL-C 26W/865/2P 1CT/5X10BOX	0.335 A	26.5 W

### Approval and Application

Order Code	Full Product Name	Energy Consumption kWh/
		1000 h
927905784001	MASTER PL-C 18W/840/2P 1CT/5X10BOX	22 kWh
927905786502	MASTER PL-C 18W/865/2P 1CT/5X10BOX	22 kWh
927906182701	MASTER PL-C 26W/827/2P 1CT/5X10BOX	32 kWh

Order Code	Full Product Name	Energy Consumption kWh/
		1000 h
927906183001	MASTER PL-C 26W/830/2P 1CT/5X10BOX	32 kWh
927906184001	MASTER PL-C 26W/840/2P 1CT/5X10BOX	32 kWh
927906186565	MASTER PL-C 26W/865/2P 1CT/5X10BOX	32 kWh

