



Product Description

MASTER PL-C 2 Pin

Energy-saving compact fluorescent lamps. Compact long-arc low-pressure mercury discharge lamp. Envelope consists of 4 parallel narrow fluorescent tubes

Benefits

- Optimal light performance for short or long operation per switch on
- Long life and sustainable light output

Features

- 2-pin base with a housing incorporating the special instant starter and capacitor
- Lamp characteristics are influenced by operating conditions and control gear used
- Dimming is not possible

Application

- Designed for general or supplementary lighting in professional or home environments
- Recessed or surface-mounted downlighters, wall units, table lamps and pendant lamps

Warnings and Safety

- Use only with electromagnetic control gear
- Lamp light technical and electrical characteristics are influenced by operating conditions, i.e. lamp ambient temperature and operating position
- Dimming is not possible
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

MASTER PL-C 2 Pin

Versions




LPPR PLC2P 13W



LPPR PLC2P 18W

Dimensional drawing



Product	D (max)	D1 (max)	A (max)	B (max)	C (max)
MASTER PL-C 13W/830/2P 1CT/5X10BOX	27.1 mm	27.1 mm	97.5 mm	117.0 mm	139.4 mm
MASTER PL-C 18W/830/2P 1CT/5X10BOX	27.1 mm	27.1 mm	109.5 mm	128.0 mm	150.4 mm

Light Technical	
Color Designation	Warm White (WW)
Correlated Color Temperature (Nom)	3000 K
Color rendering index (CRI)	82
Controls and Dimming	
Dimmable	No
Approval and Application	
Mercury (Hg) Content (Nom)	1.4 mg

General Information

Order Code	Full Product Name	Cap-Base
927904883001	MASTER PL-C 13W/830/2P 1CT/5X10BOX	G24d-1

Order Code	Full Product Name	Cap-Base
927905783001	MASTER PL-C 18W/830/2P 1CT/5X10BOX	G24d-2

Light Technical

Order Code	Full Product Name	Luminous Efficacy (rated) (Nom)	Luminous Flux
927904883001	MASTER PL-C 13W/830/2P 1CT/5X10BOX	69 lm/W	925 lm

Order Code	Full Product Name	Luminous Efficacy (rated) (Nom)	Luminous Flux
927905783001	MASTER PL-C 18W/830/2P 1CT/5X10BOX	67 lm/W	1,200 lm

MASTER PL-C 2 Pin

Operating and Electrical

Order Code	Full Product Name	Lamp Current	Power Consumption
		(Nom)	
927904883001	MASTER PL-C 13W/830/2P 1CT/5X10BOX	0.170 A	13.4 W

Order Code	Full Product Name	Lamp Current	Power Consumption
		(Nom)	
927905783001	MASTER PL-C 18W/830/2P 1CT/5X10BOX	0.230 A	17.9 W

Approval and Application

Order Code	Full Product Name	Energy Consumption kWh/
		1000 h
927904883001	MASTER PL-C 13W/830/2P 1CT/ 5X10BOX	17 kWh

Order Code	Full Product Name	Energy Consumption kWh/
		1000 h
927905783001	MASTER PL-C 18W/830/2P 1CT/ 5X10BOX	22 kWh

