



Product Description

MASTER PL-C 4 Pin

Energy-saving compact fluorescent lamps. Compact long-arc low-pressure mercury discharge lamp. Envelope consists of 4 parallel narrow fluorescent tubes

Benefits

- Optimal light performance for short or long operation per switch-on
- Optimal light performance for short or long operation per switch on
- Multiple light color choice
- Long life and sustainable light output
- Good color rendering (CRI >80)
- Dimming possible down to 10%

Features

- 4-pin base
- 4-pin base without starter and capacitor
- Fluorescent tri-phosphor technology
- Lamp characteristics are influenced by operating conditions and control gear used
- Low light depreciation over lamp life
- Dimming is possible

Application

- Designed for general or supplementary lighting in professional or home environments
- Designed for general or supplementary lighting in professional or home environments
- Recessed or surface-mounted downlighters, wall units, table lamps and pendant lamps
- Recessed or surface-mounted downlighters, wall units, table lamps and pendant lamps

MASTER PL-C 4 Pin

Warnings and Safety

- Lamp light technical and electrical characteristics are influenced by operating conditions, i.e. lamp ambient temperature and operating position as well as applied HF control gear
- Lamp light technical and electrical characteristics are influenced by operating conditions, i.e. lamp ambient temperature and operating position as well as applied HF control gear
- Shorter lamp life when often switching and not well pre-heated electrodes
- Shorter lamp life when often switching and not well pre-heated electrodes
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.


Versions



LPPR PLC4P 13W

MASTER PL-C 4 Pin

Dimensional drawing



Product	D (max)	D1 (max)	A (max)	B (max)	C (max)
MASTER PL-C 13W/827/4P 1CT/5X10BOX	27.1 mm	27.1 mm	97.5 mm	117.0 mm	131.9 mm
MASTER PL-C 13W/830/4P 1CT/5X10BOX	27.1 mm	27.1 mm	97.5 mm	117.0 mm	131.9 mm
MASTER PL-C 13W/840/4P 1CT/5X10BOX	27.1 mm	27.1 mm	97.5 mm	117.0 mm	131.9 mm
MASTER PL-C 13W/865/4P 1CT/5X10BOX	27.1 mm	27.1 mm	97.5 mm	117.0 mm	131.9 mm
MASTER PL-C 18W/827/4P 1CT/5X10BOX	27.1 mm	27.1 mm	109.5 mm	128.0 mm	142.9 mm
MASTER PL-C 18W/830/4P 1CT/5X10BOX	27.1 mm	27.1 mm	109.5 mm	128.0 mm	142.9 mm
MASTER PL-C 18W/840/4P 1CT/5X10BOX	27.1 mm	27.1 mm	109.5 mm	128.0 mm	142.9 mm
MASTER PL-C 18W/865/4P 1CT/5X10BOX	27.1 mm	27.1 mm	109.5 mm	128.0 mm	142.9 mm
MASTER PL-C 26W/830/4P 1CT/5X10BOX	27.1 mm	27.1 mm	130.5 mm	149.0 mm	163.9 mm
MASTER PL-C 26W/840/4P 1CT/5X10BOX	27.1 mm	27.1 mm	130.5 mm	149.0 mm	163.9 mm
MASTER PL-C 26W/865/4P 1CT/5X10BOX	27.1 mm	27.1 mm	130.5 mm	149.0 mm	163.9 mm

Controls and Dimming	
Dimmable	Yes
Approval and Application	
Mercury (Hg) Content (Nom)	1.4 mg

General Information

Order Code	Full Product Name	Cap-Base	Nominal lifetime
927907182701	MASTER PL-C 13W/827/4P 1CT/5X10BOX	G24q-1	-
927907183001	MASTER PL-C 13W/830/4P 1CT/5X10BOX	G24q-1	-
927907184002	MASTER PL-C 13W/840/4P 1CT/5X10BOX	G24q-1	-
927907186501	MASTER PL-C 13W/865/4P 1CT/5X10BOX	G24q-1	-
927907282701	MASTER PL-C 18W/827/4P 1CT/5X10BOX	G24q-2	-
927907283001	MASTER PL-C 18W/830/4P 1CT/5X10BOX	G24q-2	-

Order Code	Full Product Name	Cap-Base	Nominal lifetime
927907284065	MASTER PL-C 18W/840/4P 1CT/5X10BOX	G24q-2	-
927907286501	MASTER PL-C 18W/865/4P 1CT/5X10BOX	G24q-2	-
927907383001	MASTER PL-C 26W/830/4P 1CT/5X10BOX	G24q-3	10,000 hour(s)
927907384002	MASTER PL-C 26W/840/4P 1CT/5X10BOX	G24q-3	10,000 hour(s)
927907386565	MASTER PL-C 26W/865/4P 1CT/5X10BOX	G24q-3	-

Light Technical

Order Code	Full Product Name	Color Designation	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)	Luminous Flux
927907182701	MASTER PL-C 13W/827/4P 1CT/5X10BOX	Incandescent White	2700 K	82	69 lm/W	925 lm
927907183001	MASTER PL-C 13W/830/4P 1CT/5X10BOX	Warm White (WW)	3000 K	82	72 lm/W	900 lm
927907184002	MASTER PL-C 13W/840/4P 1CT/5X10BOX	Cool White (CW)	4000 K	82	69 lm/W	925 lm
927907186501	MASTER PL-C 13W/865/4P 1CT/5X10BOX	Cool Daylight	6500 K	80	63 lm/W	845 lm

MASTER PL-C 4 Pin

Order Code	Full Product Name	Color Designation	Correlated Color	Color rendering		
			Temperature (Nom)	index (CRI)	Luminous Efficacy (rated) (Nom)	Luminous Flux
927907282701	MASTER PL-C 18W/827/4P 1CT/5X10BOX	Incandescent White	2700 K	82	67 lm/W	1,200 lm
927907283001	MASTER PL-C 18W/830/4P 1CT/5X10BOX	Warm White (WW)	3000 K	82	67 lm/W	1,200 lm
927907284065	MASTER PL-C 18W/840/4P 1CT/5X10BOX	Cool White (CW)	4000 K	82	67 lm/W	1,200 lm
927907286501	MASTER PL-C 18W/865/4P 1CT/5X10BOX	Cool Daylight	6500 K	80	62.3 lm/W	1,120 lm
927907383001	MASTER PL-C 26W/830/4P 1CT/5X10BOX	Warm White (WW)	3000 K	82	67 lm/W	1,800 lm
927907384002	MASTER PL-C 26W/840/4P 1CT/5X10BOX	Cool White (CW)	4000 K	82	67 lm/W	1,800 lm
927907386565	MASTER PL-C 26W/865/4P 1CT/5X10BOX	Cool Daylight	6500 K	80	66 lm/W	1,740 lm

Operating and Electrical

Order Code	Full Product Name	Lamp Current	
		(Nom)	Power Consumption
927907182701	MASTER PL-C 13W/827/4P 1CT/5X10BOX	0.170 A	13.0 W
927907183001	MASTER PL-C 13W/830/4P 1CT/5X10BOX	0.170 A	13.0 W
927907184002	MASTER PL-C 13W/840/4P 1CT/5X10BOX	0.170 A	13.0 W
927907186501	MASTER PL-C 13W/865/4P 1CT/5X10BOX	0.170 A	13.0 W
927907282701	MASTER PL-C 18W/827/4P 1CT/5X10BOX	0.230 A	16.5 W
927907283001	MASTER PL-C 18W/830/4P 1CT/5X10BOX	0.230 A	16.5 W

Order Code	Full Product Name	Lamp Current	
		(Nom)	Power Consumption
927907284065	MASTER PL-C 18W/840/4P 1CT/5X10BOX	0.230 A	18.0 W
927907286501	MASTER PL-C 18W/865/4P 1CT/5X10BOX	0.230 A	18.0 W
927907383001	MASTER PL-C 26W/830/4P 1CT/5X10BOX	0.335 A	26.0 W
927907384002	MASTER PL-C 26W/840/4P 1CT/5X10BOX	0.335 A	26.0 W
927907386565	MASTER PL-C 26W/865/4P 1CT/5X10BOX	0.335 A	26.0 W

Approval and Application

Order Code	Full Product Name	Energy Consumption kWh/
		1000 h
927907182701	MASTER PL-C 13W/827/4P 1CT/5X10BOX	15 kWh
927907183001	MASTER PL-C 13W/830/4P 1CT/5X10BOX	15 kWh
927907184002	MASTER PL-C 13W/840/4P 1CT/5X10BOX	15 kWh
927907186501	MASTER PL-C 13W/865/4P 1CT/5X10BOX	15 kWh
927907282701	MASTER PL-C 18W/827/4P 1CT/5X10BOX	20 kWh
927907283001	MASTER PL-C 18W/830/4P 1CT/5X10BOX	20 kWh

Order Code	Full Product Name	Energy Consumption kWh/
		1000 h
927907284065	MASTER PL-C 18W/840/4P 1CT/5X10BOX	20 kWh
927907286501	MASTER PL-C 18W/865/4P 1CT/5X10BOX	20 kWh
927907383001	MASTER PL-C 26W/830/4P 1CT/5X10BOX	29 kWh
927907384002	MASTER PL-C 26W/840/4P 1CT/5X10BOX	29 kWh
927907386565	MASTER PL-C 26W/865/4P 1CT/5X10BOX	29 kWh

