



产品描述

MASTER PL-C 4 针

紧凑型节能荧光灯。紧凑的长弧结构，低压低汞荧光灯管。由 4 根平行的细荧光灯管组成

优点

- 光照性能最优化，每次点亮后可短时或长时工作
- 长寿命和可持续光输出

特点

- 2 针特殊灯座，内装抗干扰的电容和启动器，不可调光
- 4 针灯座，无启动器和电容器；适合与高频电子镇流器配用；若与电感镇流器配用，则须加装启动器；用户可选用适当的镇流器，用于调节灯光的明暗度
- 应用环境和配套镇流器会影响光源的性能
- 适合与电子调节装置一同使用，实现可控制的光输出、HF 操作并可独立于供电系统之外

应用

- 为专业及家庭环境的一般照明或辅助照明而设计
- 用于嵌入式或吸顶式筒灯、壁灯、台灯和吸顶灯灯具

安全提示

- Lamp light technical and electrical characteristics are influenced by operating conditions, i.e. lamp ambient temperature and operating position as well as applied HF control gear
- Shorter lamp life when often switching and not well pre-heated electrodes
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

MASTER PL-C 4 针

Versions



LPPR PLC4P 13W




LPPR PLC4P 18W



LPPR PLC4P 26W

二维绘图



Product	D (max)	D1 (max)	A (max)	B (max)	C (max)
MASTER PL-C 13W/840/4P 1CT/ 5X10BOX	27.1 mm	27.1 mm	97.5 mm	117.0 mm	131.9 mm
MASTER PL-C 18W/830/4P 1CT/ 5X10BOX	27.1 mm	27.1 mm	109.5 mm	128.0 mm	142.9 mm
MASTER PL-C 26W/827/4P 1CT/ 5X10BOX	27.1 mm	27.1 mm	130.5 mm	149.0 mm	163.9 mm
MASTER PL-C 26W/840/4P 1CT/ 5X10BOX	27.1 mm	27.1 mm	130.5 mm	149.0 mm	163.9 mm
MASTER PL-C 26W/865/4P 1CT/ 5X10BOX	27.1 mm	27.1 mm	130.5 mm	149.0 mm	163.9 mm

控制和调光	
可调光	是
审批和申请	
汞 (Hg) 含量 (标称)	1.4 mg

一般信息

Order Code	Full Product Name	底盖	标称使用寿命
927907184002	MASTER PL-C 13W/840/4P 1CT/5X10BOX	G24q-1	-
927907283001	MASTER PL-C 18W/830/4P 1CT/5X10BOX	G24q-2	-
927907382701	MASTER PL-C 26W/827/4P 1CT/5X10BOX	G24q-3	-

Order Code	Full Product Name	底盖	标称使用寿命
927907384002	MASTER PL-C 26W/840/4P 1CT/5X10BOX	G24q-3	10,000 小时
927907386565	MASTER PL-C 26W/865/4P 1CT/5X10BOX	G24q-3	-

灯技术

Order Code	Full Product Name	颜色名称	相关色温 (标称)	显色指数 (CRI)	光效 (额定)(标称)	光通量
927907184002	MASTER PL-C 13W/840/4P 1CT/5X10BOX	冷白色 (CW)	4000 K	82	69 lm/W	925 lm
927907283001	MASTER PL-C 18W/830/4P 1CT/5X10BOX	暖白色 (WW)	3000 K	82	67 lm/W	1,200 lm
927907382701	MASTER PL-C 26W/827/4P 1CT/5X10BOX	白炽灯白光	2700 K	82	67 lm/W	1,800 lm
927907384002	MASTER PL-C 26W/840/4P 1CT/5X10BOX	冷白色 (CW)	4000 K	82	67 lm/W	1,800 lm
927907386565	MASTER PL-C 26W/865/4P 1CT/5X10BOX	冷日光	6500 K	80	66 lm/W	1,740 lm

MASTER PL-C 4 针

操作和电气

Order Code	Full Product Name	灯具电流 (标称) 功耗	
927907184002	MASTER PL-C 13W/840/4P 1CT/5X10BOX	0.170 A	13.0 W
927907283001	MASTER PL-C 18W/830/4P 1CT/5X10BOX	0.230 A	16.5 W
927907382701	MASTER PL-C 26W/827/4P 1CT/5X10BOX	0.335 A	26.0 W

Order Code	Full Product Name	灯具电流 (标称) 功耗	
927907384002	MASTER PL-C 26W/840/4P 1CT/5X10BOX	0.335 A	26.0 W
927907386565	MASTER PL-C 26W/865/4P 1CT/5X10BOX	0.335 A	26.0 W

审批和申请

Order Code	Full Product Name	能耗 kWh/1000 h
927907184002	MASTER PL-C 13W/840/4P 1CT/5X10BOX	15 kWh
927907283001	MASTER PL-C 18W/830/4P 1CT/5X10BOX	20 kWh
927907382701	MASTER PL-C 26W/827/4P 1CT/5X10BOX	29 kWh

Order Code	Full Product Name	能耗 kWh/1000 h
927907384002	MASTER PL-C 26W/840/4P 1CT/5X10BOX	29 kWh
927907386565	MASTER PL-C 26W/865/4P 1CT/5X10BOX	29 kWh

