



# Green Flagship product as best environmental choice in the energy saving lamps portfolio

## MASTER PL-Electronic Polar

Energy-saving covered lamps for outdoor professional applications – the perfect choice for end-users who demand the best performance and reliability The product family offers different wattages to suit different applications

### Faydaları

- The perfect choice for extreme temperature resistant with best performance & reliability
- Save your money with long life-time and high energy efficiency
- Lifetime independent of switching on-off

### Özellikler

- Lightweight, superior long-life and energy saving alternative to incandescent lamps
- Very Suitable for frequent switching
- Very good lumen maintenance throughout the lifetime of the lamp
- Fast Run-up
- Suitable for emergency lighting with DC supply

## MASTER PL-Electronic Polar


### Uygulama

- Designed to replace incandescent lamps in most professional and semi-professional applications
- Enclosed fixtures required for outdoor applications
- Not suitable for use with dimmers or electronic gear

### Versions



### Boyutlu çizim



Product	D (max)	C (max)	F (max)
MASTER PL-E Polar 23W/827 E27 1CH/6	50,8 mm	158,0 mm	48,0 mm

