



True color rendering!

MASTER PL-L De Luxe 4 Pin

MASTER PL-L De Luxe is a medium to high-wattage linear compact fluorescent lamp, typically used for general-illumination ceiling luminaires in retail, hospitality and office applications demanding higher lighting levels and excellent color rendering. The original Philips-invented bridge technology guarantees optimum performance in the application, enabling more light and higher efficacy than the bended technology. It is designed for operation on electromagnetic as well as electronic HF control gear and is provided with a plug-in/pull-out lamp base.

Benefits

- Excellent light performance for short or long operation per switch-on
- Long life
- Multiple light color choice
- Excellent color rendering (CRI >90)
- Dimming possible down to 10%

Features

- 4-pin base
- Fluorescent technology
- High-end phosphor coating

Application

- Used in applications where good colour rendering is of a very high importance, such as shops (clothing, paint etc.), hairdressers, medical environments, museums, exhibition areas, graphics & printing industry etc.


MASTER PL-L De Luxe 4 Pin

Versions



55W, 2G11, 4P

Dimensional drawing



Product	D (max)	D1 (max)	A (max)	B (max)	C (max)
MASTER PL-L 90 De Luxe 55W/ 930/4P 1CT/10	39.0 mm	18.0 mm	509.2 mm	535 mm	541.6 mm

