



# Product Description

## PL-Q 2 Pin

Compact fluorescent lamps with a quadrant-like shape

### Benefits

- High light quality and optimum lumen output provide increased value for money
- Energy-saving light with good colour rendering
- Long service lifetime
- The Philips Lighting stamp of quality

### Features

- Retrofit in already installed 2D luminaires
- Assembled with the same high-quality components as all other Philips CFL-NI lamps

### Application

- Ideal for applications such as
- corridors
- toilets
- stairwells
- reception areas

### Warnings and Safety

- Use only with electromagnetic control gear
- Lamp light technical and electrical characteristics are influenced by operating conditions, i.e. lamp ambient temperature and operating position
- Dimming is not possible
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.