



# Product Description

## MASTER PL-T TOP 4 Pin

Energy saving compact fluorescent lamp. Compact long-arc low-pressure mercury discharge lamp. Envelope consists of 6 parallel narrow fluorescent tubes. Amalgam controlled operation

### Benefits

- Optimal lighting performance for long periods of continuous operation
- Substantially higher light output (+30%) per light point than conventional solutions
- High temperature independency at higher application temperatures
- Long life and sustainable light output

### Features

- 4-pin base without glow switch starter and capacitor
- Hot restrike - moderate light run up after cooling down at low temperatures
- Optimized lighting performance over a broad temperature range due to Philips amalgam technology
- Dimming is possible

### Application

- Designed for general or supplementary lighting in professional and semi-professional environments
- Ideal for use in recessed or surface mounted downlighters, wall units
- First choice for long switching cycles and highest light output

### Warnings and Safety

- Lamp light technical and electrical characteristics are influenced by operating conditions, i.e. lamp ambient temperature and operating position as well as applied HF control gear
- Shorter lamp life when often switching and not well pre-heated electrodes
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.


# MASTER PL-T TOP 4 Pin

## Versions



LPPR PLTTOP4P 42W

## Dimensional drawing



Product	D (max)	A (max)	B (max)	C (max)
MASTER PL-T TOP 42W/840/4P 1CT/ 5X10BOX	41 mm	120.7 mm	145.0 mm	160.7 mm

