



Combining superior high lumen, design & performance

Twister High Lumen

Energy saving lamp in spiral shape, with superior performance (long life, high switching) and high lumen warm bright light. Perfectly suitable to be used in places where high lumen is required, and the lamp is directly visible.

Benefícios

- Simple installation – no ballast needed
- Save your money with long life-time
- Perfect energy-saving solution for mercury lamps replacement

Características

- Long-Life and Energy saving alternative to Incandescent lamps
- Suitable for frequent switching
- Flawless ignition at -10°C and up
- Ambient temperature range to ensure almost constant light output: 0 - 50°C

Aplicação


- Desenvolvida principalmente para aplicações profissionais (hotéis, restaurantes, lojas), idealmente aplicações indoor com elevada altura (high bay)
- não compatível com dimmers ou reatores eletrônicos.

Twister High Lumen

Versions



Desenho dimensional



Product	D (max)	C (max)	F (max)
Twister High Lumen 45W CDL E27 LV 1CT/6	82 mm	200 mm	67 mm

