

Long-lasting, reliable solution

HID-Basic BSN/BMH series multi-wattage for SON/CDO/CDM/MH/HPI

Impregnated electromagnetic copper/iron double-wattage ballasts for use with an external series (superimposed) ignitor for CDO, MH, HPI (Plus) and SON lamps

Benefits

- Up to 40% energy saving using power-reduction controllers
- Minimal watt losses thanks to orthocyclic winding process
- Long-lasting reliable solution protected from overheating

Features

- Possibility of dimming with an external controller
- Multi-wattage ballasts can be used only in series circuits
- Equipped with screw terminal blocks as standard; insert contacts available upon request
- Earthing-while-mounting facility
- Ballasts for alternative mains voltages/frequencies available upon request

Application



- Outdoor lighting

HID-Basic BSN/BMH series multi-wattage for SON/CDO/CDM/MH/HPI

Versions



Dimensional drawing



Product	A1	A2	B1	C1	D1
BSN 70/50 K302-A2-TS 230V 50Hz	123 mm	98 mm	61 mm	52 mm	6.2 mm

