



產品說明

MASTERColour CDM-R 陶瓷複金屬燈

精巧、高效率放電式反射燈具，光色歷久如新，光線清晰明亮

优点

- 高效率燈具，節省電費支出，降低光照熱度
- 使用壽命優於白熾燈與鹵素燈
- 歷久如新的穩定光色
- 設計獨特，提升應用彈性，更讓如此小巧低調的燈具，帶來強大大照明效果
- CDM-R 燈管可用於開放式燈具，大幅簡化燈具設計
- 熱度較其他燈具為低，使顧客與工作人員更感舒適
- 內建紫外線濾鏡，減少商品褪色風險

特点

- 清晰明亮的白色光
- 絕佳的演色性
- 輕巧型反射燈，提供高強度光束，既簡單又有效率

应用


- 店面和商品櫥窗、辦公室與公共建築
- 戶外裝飾照明：泛光照明與行人徒步區

安全提示

- Control gear must include end-of-life protection (IEC61167, IEC 62035)
- Use only with electronic control gear. Color 830 lamps may also use electromagnetic gear.
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

MASTERColour CDM-R 陶瓷複金屬燈

二维绘图



Product	D (max)	D	C (max)	C
MASTERC CDM-R 35W/830 E27 PAR20 30D 1CT	65 mm	64 mm	95 mm	92 mm

Product	D (max)	D	C (max)	C
MASTERC CDM-R 35W/830 E27 PAR30L 30D 1CT	97 mm	95 mm	123 mm	120 mm
MASTERC CDM-R 70W/830 E27 PAR30L 40D 1CT	97 mm	95 mm	123 mm	120 mm

一般資訊	
燈座基底	E27
操作位置	UNIVERSAL
照明技術	
色彩名稱	暖白光 (WW)
相關色彩溫度 (規範)	3000 K
演色性指數 (CRI)	81
運轉與電力	
達到 60% 光色的熱機時間	120 s
控制與調光	
可調光	否
機械與外罩	
燈泡表層	透明

Order Code	Full Product Name	切換週期
928071000691	MASTERC CDM-R 35W/830 E27 PAR30L 30D 1CT	1,000
928071200691	MASTERC CDM-R 70W/830 E27 PAR30L 40D 1CT	1,050
928084000691	MASTERC CDM-R 35W/830 E27 PAR20 30D 1CT	800

照明技術 (1/2)

Order Code	Full Product Name	光束角 (Nom)	色度坐標 X (標稱)	色度坐標 Y (Nom)	LLMF 標稱 壽命結束 (規範)
928071000691	MASTERC CDM-R 35W/830 E27 PAR30L 30D 1CT	30 °	0.431	0.400	48 %
928071200691	MASTERC CDM-R 70W/830 E27 PAR30L 40D 1CT	40 °	0.427	0.397	62 %

Order Code	Full Product Name	光束角 (Nom)	色度坐標 X (標稱)	色度坐標 Y (Nom)	LLMF 標稱 壽命結束 (規範)
928084000691	MASTERC CDM-R 35W/830 E27 PAR20 30D 1CT	30 °	0.433	0.402	52 %

MASTERColour CDM-R 陶瓷複金屬燈

照明技術 (2/2)

Order Code	Full Product Name	光通量	光強 (標稱)
928071000691	MASTERC CDM-R 35W/830 E27 PAR30L 30D 1CT	-	7,400 cd
928071200691	MASTERC CDM-R 70W/830 E27 PAR30L 40D 1CT	4,500 lm	9,500 cd

Order Code	Full Product Name	光通量	光強 (標稱)
928084000691	MASTERC CDM-R 35W/830 E27 PAR20 30D 1CT	-	5,300 cd

運轉與電力

Order Code	Full Product Name	電壓 (標稱)	耗電量
928071000691	MASTERC CDM-R 35W/830 E27 PAR30L 30D 1CT	86 V	39.1 W
928071200691	MASTERC CDM-R 70W/830 E27 PAR30L 40D 1CT	90 V	73.2 W

Order Code	Full Product Name	電壓 (標稱)	耗電量
928084000691	MASTERC CDM-R 35W/830 E27 PAR20 30D 1CT	88 V	39.1 W


機械與外罩


Order Code	Full Product Name	燈泡形狀
928071000691	MASTERC CDM-R 35W/830 E27 PAR30L 30D 1CT	PAR30L
928071200691	MASTERC CDM-R 70W/830 E27 PAR30L 40D 1CT	PAR30L

Order Code	Full Product Name	燈泡形狀
928084000691	MASTERC CDM-R 35W/830 E27 PAR20 30D 1CT	PAR20

認證與應用


Order Code	Full Product Name	能源消耗 kWh/1000 h	汞 (Hg) 含量 (標稱)
928071000691	MASTERC CDM-R 35W/830 E27 PAR30L 30D 1CT	42 kWh	2.8 mg
928071200691	MASTERC CDM-R 70W/830 E27 PAR30L 40D 1CT	80 kWh	8.3 mg
928084000691	MASTERC CDM-R 35W/830 E27 PAR20 30D 1CT	42 kWh	2.8 mg






MASTERColour CDM-R 陶瓷複金屬燈


Accent Diagrams



Accent Diagram - MASTERC CDM-R 70W/830
E27 PAR30L 40D 1CT




Accent Diagram - MASTERC CDM-R 35W/830
E27 PAR20 30D 1CT




Accent Diagram - MASTERC CDM-R 35W/830
E27 PAR30L 30D 1CT


Beam Diagrams



Beam diagram - MASTERC CDM-R 70W/830
E27 PAR30L 40D 1CT



Beam diagram - MASTERC CDM-R 35W/830
E27 PAR20 30D 1CT



Beam diagram - MASTERC CDM-R 35W/830
E27 PAR30L 30D 1CT

