



# Beautiful sparkle, reliable life

## MASTERColour CDM-TC

Range of single-ended, very compact, high-efficiency, discharge lamps with a stable color over lifetime and a crisp, sparkling light

### Benefits

- Long lamp life compared with incandescent and halogen lamps
- UV-Block quartz outer bulb for reduced fading risks
- Stable color impression over lifetime
- High lamp efficacy results in low operating costs and low heat generation (which enhances comfort for shoppers and staff)

### Features

- Crisp white light
- Superior color quality
- Allows very small-size luminaires designs that give high beam intensities

### Application

- Accent lighting display lighting with sparkling effect
- General and decorative lighting

### Warnings and Safety

- Use only in totally enclosed luminaire, even during testing (IEC61167, IEC 62035, IEC60598)
- The luminaire must be able to contain hot lamp parts if the lamp ruptures
- Control gear must include end-of-life protection (IEC61167, IEC 62035)
- Use only with electronic control gear. 35W/830 lamps may also use electromagnetic gear.
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.


# MASTERColour CDM-TC

## Versions



CDM-TC, 35W

## Dimensional drawing



| Product                                    | D (max) | D      | O    | L (min) | L (max) | L     | C (max) |
|--|---------|--------|------|---------|---------|-------|---------|
| MASTERColour CDM-TC<br>35W/842 G8.5 1CT/12 | 15 mm   | 0.5 in | 5 mm | 51 mm   | 53 mm   | 52 mm | 85 mm   |

