



# Product Description

## MASTERColour CDM-T Elite

Single-ended, high-efficiency Ceramic Metal Halide discharge lamp

### Benefits

- Outstanding rendering of displayed merchandise due to high colour rendering (Ra 90) in combination with high lumen output; best offer in the market for 'enhancing merchandize'
- Excellent colour quality, which remains stable over lifetime
- Light output over lifetime maintains display brightness
- High efficacy and long lifetime for lowest operating costs and low heat generation
- Relatively low heat generation enhances comfort for shoppers and staff
- UV Block for reduced fading risk of merchandise

### Features

- Crisp white light
- Excellent colour rendering (Ra 90)
- Reliable lifetime performance
- Stable colour performance during lifetime
- Increased light output compared with regular MASTERColour lamps
- Improved maintenance compared with regular MASTERColour lamps
- Burning position for
  - CDM Elite-T 35W: vertical +/- 60 degrees
  - CDM Elite-T 70W: universal

### Application

- Accent and display lighting with a sparkling effect, excellent solution for Retail
- Decorative outdoor floodlighting

# MASTERCoulour CDM-T Elite


## Warnings and Safety

- Use only in totally enclosed luminaire, even during testing (IEC61167, IEC 62035, IEC60598)
- The luminaire must be able to contain hot lamp parts if the lamp ruptures
- Use only with electronic control gear. 35W & 70W lamps may also use electromagnetic gear.
- Control gear must include end-of-life protection (IEC61167, IEC 62035)
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

## Versions



## Dimensional drawing



Product	D (max)	O	L (min)	L (max)	L	C (max)
MASTERC CDM-T Elite 35W/930 G12 1CT/12	20 mm	4.8 mm	55 mm	57 mm	56 mm	103 mm
MASTERC CDM-T Elite 70W/930 G12 1CT/12	20 mm	7.15 mm	55 mm	57 mm	56 mm	103 mm

# MASTERColour CDM-T Elite

General Information	
Cap-Base	G12
Operating Position	UNIVERSAL
Light Technical	
Chromaticity Coordinate X (Nom)	0.435
Color Designation	Warm White (WW)
Correlated Color Temperature (Nom)	3000 K
Color rendering index (CRI)	90
Operating and Electrical	
Voltage (Nom)	85 V
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Finish	Clear
Bulb Shape	T19

## Light Technical

Order Code	Full Product Name	Chromaticity	Luminous Efficacy (rated)
		Coordinate Y (Nom)	(Nom)
928185205129	MASTERC CDM-T Elite 35W/930 G12 1CT/12	0.395	98 lm/W
928185305129	MASTERC CDM-T Elite 70W/930 G12 1CT/12	0.396	103 lm/W

## Operating and Electrical

Order Code	Full Product Name	Power Consumption
928185205129	MASTERC CDM-T Elite 35W/930 G12 1CT/12	39.1 W

Order Code	Full Product Name	Power Consumption
928185305129	MASTERC CDM-T Elite 70W/930 G12 1CT/12	73.2 W

## Approval and Application

Order Code	Full Product Name	Energy Consumption	Mercury (Hg)
		kWh/1000 h	Content (Nom)
928185205129	MASTERC CDM-T Elite 35W/930 G12 1CT/12	43 kWh	4.7 mg
928185305129	MASTERC CDM-T Elite 70W/930 G12 1CT/12	80 kWh	6.6 mg

