



Perfect sparkle, mini design

MASTERColour CDM-Tm Elite Mini

Mini, single-ended, very high-efficiency, long-life Ceramic Metal Halide discharge lamp producing crisp white sparkling light with high colour rendering

Benefits

- High-intensity beam of crisp white sparkling light makes merchandise look irresistible
- High-intensity beam of crisp white sparkling light makes merchandise look irresistible
- Lowest Total Cost of Ownership as a result of high efficacy (same light, less energy or same energy, more light) and long life
- Lowest Total Cost of Ownership as a result of high efficacy (same light, less energy or same energy, more light) and long life
- Fits in small luminaires which are less visible
- Fits in small luminaires which are less visible

Features

- Crisp white sparkling light
- Crisp white sparkling light
- Excellent color rendering, with extra red
- Excellent colour rendering, with extra red
- High efficacy with unparalleled lumen maintenance
- High efficacy with unparalleled lumen maintenance
- Stable color performance over lifetime
- Stable colour performance over lifetime
- Mini size
- Mini size

MASTERColour CDM-Tm Elite Mini

Application

- Accent and display lighting in retail
- Accent and display lighting in retail
- General and decorative indoor lighting
- General and decorative indoor lighting
- Outdoor area lighting
- Outdoor area lighting

Warnings and Safety


- Use only in totally enclosed luminaire, even during testing (IEC61167, IEC 62035, IEC60598)
- Use only in totally enclosed luminaire, even during testing (IEC61167, IEC 62035, IEC60598)
- The luminaire must be able to contain hot lamp parts if the lamp ruptures
- The luminaire must be able to contain hot lamp parts if the lamp ruptures
- Use only with electronic control gear
- Use only with electronic control gear
- For 50W use with Philips electronic gear only
- For 50W use with Philips electronic gear only
- Control gear must include end-of-life protection (IEC61167, IEC 62035)
- Control gear must include end-of-life protection (IEC61167, IEC 62035)
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Versions



LPPR CDM-Tm 0001

Dimensional drawing



Product	D (max)	D	O	L (min)	L (max)	L	C (max)
MC CDM-Tm Elite Mini	13.3 mm	0.5 inch	3.4 mm	28 mm	32 mm	30 mm	56.7 mm
20W/830 GU6.5 1CT							

MASTERColour CDM-Tm Elite Mini

