



产品说明

MASTERColour CDM-T 精锐型(MW)

MASTERColour CDM Elite MW——中等功率照明系统，能够输出持续时间更长的优质白光，既可用于室内也可用于室外

优点

- 高效的光源和驱动器意味着能耗更低，二氧化碳的排放量也相应减少，而光线质量始终如一。
- 更长的服务寿命相当于降低了维护和更换成本。
- 从始至终均能呈现卓越的光色和持续的光输出
- 与传统的 HPI 及 HPL 光源相比，外型小 50%，给光学器件和光源设计师充分的自由。
- 由于现在 CDM 光源可以用于许多新的应用场合，故照明设计实现了更高的和谐性
- 闪烁的白光使其更接近自然光的效果，营造诱人氛围

特点

- 输出通透白光，具有卓越的显色性(Ra 90)
- 整个寿命期内均有稳定的光色表现以及光输出
- 新的灯座设计使光源的外型更加紧凑，还提高了能效及配光
- 电子驱动器既可用于室内也可用于室外
- 对现有 CDM 光源进行补充 产品范围扩展至 20W 到 315W

应用


- 室外; 用作建筑物或其它结构的泛光照明 用于道路及人行道区域、公共空间、停车场以及加油站等场所的照明
- 室内；大型零售卖场（高棚）、仓库及制造车间等

安全提示

- Use only in totally enclosed luminaire, even during testing, except for protected versions with PGZX18 cap, which are designed for open luminaires (IEC61167, IEC 62035, IEC60598)
- The luminaire must be able to contain hot lamp parts if the lamp ruptures
- Use only with electronic control gear
- Control gear must include end-of-life protection (IEC61167, IEC 62035)
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

MASTERColour CDM-T 精锐型(MW)

二维绘图



Product	D (max)	D	D	C (max)	C
MASTERC CDM-TMW Elite 315W/930 1CT/12	29 mm	1.1 in	28 mm	188 mm	186 mm
MASTERC CDM-TMW Elite 315W/942 1CT/12	29 mm	1.1 in	28 mm	188 mm	186 mm





一般信息	
底盖	PGZ18
操作位置	UNIVERSAL
操作和电气	
电压 (标称)	100 V
功耗	315.9 W
机械和外壳	
灯泡外观	透明
灯泡外形	TMW28
审批和申请	
能耗 kWh/1000 h	347 kWh

灯技术

Order Code	Full Product Name	色度坐标 X (标称)	色度坐标 Y (标称)	颜色名称	相关色温 (标称)	显色指数 (CRI)	光效 (额定) (最低)	光效 (额定) (标称)
928601164634	MASTERC CDM-TMW Elite 315W/930 1CT/12	0.429	0.398	暖白色 (WW)	-	90	112 lm/W	120 lm/W
928601164834	MASTERC CDM-TMW Elite 315W/942 1CT/12	0.376	0.379	冷白色 (CW)	4140 K	93	105 lm/W	112 lm/W

审批和申请

Order Code	Full Product Name	汞 (Hg) 含量 (最高)
928601164634	MASTERC CDM-TMW Elite 315W/930 1CT/12	28 mg
928601164834	MASTERC CDM-TMW Elite 315W/942 1CT/12	25 mg



MASTERColour CDM-T 精锐型(MW)

