



Product Description

MASTERColour CDM-TT

High-intensity discharge lamps with a CDM discharge tube inside a SON lamp clear tubular outer bulb

Benefits

- Runs on SON gear so directly replaces equivalent wattage SON lamp for simple upgrade from yellow to white light

Features

- Robust lamp giving a pleasant white light and a stable colour over lifetime
- Good colour rendering
- Dimming not recommended because of negative effects on lamp performance (lumen maintenance, colour and life)

Application


- City centres, shopping centres and pedestrian areas, residential areas, road lighting
- City beautification: decorative lighting and floodlighting

Versions



MASTERColour CDM-TT

Dimensional drawing



Product	D (max)	O	L	C (max)
MASTERColour CDM-TT 150W/942 E40 1SL/12	46 mm	8 mm	133 mm	211 mm

Light Distribution Diagrams

