



The easy-fitting solution for highly energy-efficient and reliable white light outdoors

MASTER CosmoWhite CPO-TT Xtra

New-generation ceramic metal-halide tubular lamps used in outdoor applications, offering efficient and pleasant white light

Benefits

- Attractive white-light alternative to current standard mercury-vapor, HPS and ceramic solutions
- Offering easy access to low-cost high-performance new system with existing standard components
- Best combination of low investment and high energy savings (up to 65%), resulting in very low cost of ownership

Features

- Highly efficient white light; extremely high system efficacy
- Long reliable lifetime; new Xtra range offering service life of up to 6 years (> 30kh average life)
- Unique new burner design in combination with glass outer bulb and Edison lamp base offering easy fit into existing HPS / SON luminaire platform
- Designed for electronic gear platforms including all control features and dimming options offering flexible light levels and reduced energy consumption

MASTER CosmoWhite CPO-TT Xtra

Application

- Street lighting and area lighting, urban and residential areas and city centers; for functional lighting and city beautification

Warnings and Safety



- Use only in a totally enclosed luminaire, even during testing (IEC 61167, IEC 62035, IEC 60598)
- The luminaire must be able to contain hot lamp parts if the lamp ruptures
- Use only with suitable electronic control gear
- Control gear must include end-of-life protection (IEC 61167, IEC 62035)
- E27 lamp holders and other parts in luminaires should be designed to withstand the ignition voltage of the electronic control gear (rated at 5 kV ignition pulse)
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Versions



LPPR CPO-TT 0002

Dimensional drawing



| Product | D (max) | D | O | L | C (max) |
|----------------------------------------|---------|-------|-------|--------|---------|
| MST CosmoWhite CPO-TT Xtra 90W/628 E40 | 47 mm | 46 mm | 18 mm | 132 mm | 211 mm |

MASTER CosmoWhite CPO-TT Xtra

