



The most energy-efficient reliable white light solution for Outdoor

MASTER CosmoWhite CPO-TW & CPO-TW Xtra

New-generation ceramic metal halide lamps used in Outdoor offering efficient and pleasant white light

Benefits

- Attractive white light
- Best optical efficacy allows greater spacing between luminaires, thereby reducing investment
- Highest energy saving and lowest cost of ownership

Features

- Highly efficient white light
- Long reliable lifetime combined with highest system efficacy
- Unique new burner design and positioning in combination with best lamp fixation (PGZ12) provides best optical efficacy
- Compact size: 50% smaller than SON/HPL systems
- New electronic gear platform including dimming options

Application

- Urban public lighting for city centers, residential areas and roads

MASTER CosmoWhite CPO-TW & CPO-TW Xtra


Warnings and Safety

- Use only in totally enclosed luminaire, even during testing (IEC61167, IEC 62035, IEC60598)
- The luminaire must be able to contain hot lamp parts if the lamp ruptures
- Use only with electronic control gear
- Control gear must include end-of-life protection (IEC61167, IEC 62035)

Versions



Dimensional drawing



Product

MASTER CosmoWhite CPO-TW Xtra 45W/628 PGZ12

150°

MASTER CosmoWhite CPO-TW & CPO-TW Xtra

