



# Product Description

## HID-Constant wattage BSX for SOX

Constant-wattage (potted) electromagnetic copper/iron ballasts for use with an external ignitor for SOX and SOX-E lamps

### Benefits

- Excellent resistance to humid conditions
- Long-lasting reliable solution – outstanding product lifetime of 15 years average
- Minimal watt losses thanks to orthocyclic winding process
- Control gear can be installed remotely

### Features

- Series capacitor required in circuits with constant wattage
- Silicon potted ballast under IP21 canopy
- Equipped with screw terminal blocks as standard
- Ballasts for alternative mains voltages/frequencies available upon request

### Application

- Ideal for the following applications:
- Road lighting, railway marshalling yards and crossings, airports, harbors and docks, quarries, foundries and rolling mills
- Security and orientation lighting
- Climatic suitability: restricted to built-in situations where relative humidity is limited