



Long-lasting, reliable solution

HID-Constant wattage BSX for SOX

Constant-wattage (potted) electromagnetic copper/iron ballasts for use with an external ignitor for SOX and SOX-E lamps

Benefits

- Excellent resistance to humid conditions
- Long-lasting reliable solution – outstanding product lifetime of 15 years average
- Minimal watt losses thanks to orthocyclic winding process
- Control gear can be installed remotely

Features


- Series capacitor required in circuits with constant wattage
- Silicon potted ballast under IP21 canopy
- Equipped with screw terminal blocks as standard
- Ballasts for alternative mains voltages/frequencies available upon request

Application

- Outdoor lighting

HID-Constant wattage BSX for SOX

Versions



Dimensional drawing

Δ 1

Product	D1	C1	A1	A2	B1	B2
BSX 135 H96	4.2 mm	67.0	149.0	135.0	80.0	42.0
220-240V 50Hz		mm	mm	mm	mm	mm
CW-149/67						

