



# Product Description

## MASTER HPI Plus

Quartz metal halide lamps with opalized outer bulb

### Benefits

- High safety and comfort level, maintained over life
- High safety and comfort level, maintained over life
- Minimal maintenance cost
- Minimal maintenance cost
- Initial investment saving options with "Plus"-concept and "S" and "P"-types
- Initial investment saving options with "Plus"-concept and "S" and "P"-types
- Adjustable atmosphere creation by using appropriate color temperature
- Adjustable atmosphere creation by using appropriate colour temperature

### Features

- Ovoid, internally white coated outer bulb
- Ovoid, internally white coated outer bulb
- Unique 3-band technology resulting in high luminous efficacy, both initially and over long lifetime
- Unique 3-band technology resulting in high luminous efficacy, both initially and over long lifetime
- Available in cool white and daylight color appearance demonstrating good color stability
- Available in cool white and daylight colour appearance demonstrating good colour stability
- "S"-type for direct retrofit for HPL lamps
- "S"-type for direct retrofit for HPL lamps
- "P"-type for use without protective front shield
- "P"-type for use without protective front shield

# MASTER HPI Plus

## Application

- High bay lighting, e.g. industrial workshops, exhibition halls, hypermarkets, shopping malls, DIY stores, churches, airports and train stations
- High bay lighting, e.g. industrial workshops, exhibition halls, hypermarkets, shopping malls, DIY stores, churches, airports and train stations

## Warnings and Safety


- Use only in totally enclosed luminaire, even during testing (IEC61167, IEC 62035, IEC60598)
- Use only in totally enclosed luminaire, even during testing (IEC61167, IEC 62035, IEC60598)
- The luminaire must be able to contain hot lamp parts if the lamp ruptures
- The luminaire must be able to contain hot lamp parts if the lamp ruptures
- For use with control gear designed for high-pressure mercury or sodium lamps
- For use with control gear designed for high-pressure mercury or sodium lamps
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

## Versions



LPPR HPI

## Dimensional drawing



Product	D (max)	C (max)
MASTER HPI Plus 250W/645 BU E40 1SL/12	91 mm	226 mm
MASTER HPI Plus 400W/645 BU E40 1SL/6	122 mm	290 mm

# MASTER HPI Plus

## General Information

Cap-Base	E40
Operating Position	H15

## Light Technical

Color Designation	Cool White (CW)
Correlated Color Temperature (Nom)	4500 K
Color rendering index (CRI)	65

## Controls and Dimming

Dimmable	No
----------	----

## Mechanical and Housing

Bulb Finish	Coated glass
-------------	--------------

## Light Technical

Order Code	Full Product Name	Chromaticity Coordinate X (Nom)	Chromaticity Coordinate Y (Nom)	Luminous Efficacy (rated) (Nom)
928074309891	MASTER HPI Plus 400W/645 BU E40 1SL/6	367	374	80 lm/W

Order Code	Full Product Name	Chromaticity Coordinate X (Nom)	Chromaticity Coordinate Y (Nom)	Luminous Efficacy (rated) (Nom)
928076709891	MASTER HPI Plus 250W/645 BU E40 1SL/12	365	363	66 lm/W

## Operating and Electrical

Order Code	Full Product Name	Voltage (Nom)	Power Consumption
928074309891	MASTER HPI Plus 400W/645 BU E40 1SL/6	125 V	405 W

Order Code	Full Product Name	Voltage (Nom)	Power Consumption
928076709891	MASTER HPI Plus 250W/645 BU E40 1SL/12	128 V	256 W

## Mechanical and Housing

Order Code	Full Product Name	Bulb Shape
928074309891	MASTER HPI Plus 400W/645 BU E40 1SL/6	BD120

Order Code	Full Product Name	Bulb Shape
928076709891	MASTER HPI Plus 250W/645 BU E40 1SL/12	BD90

## Approval and Application

Order Code	Full Product Name	Energy Consumption kWh/1000 h	Mercury (Hg) Content (Nom)
928074309891	MASTER HPI Plus 400W/645 BU E40 1SL/6	446 kWh	67 mg
928076709891	MASTER HPI Plus 250W/645 BU E40 1SL/12	282 kWh	47 mg

