



Product Description

HPL-N

Standard High Pressure Mercury lamp

Benefits

- Good budget alternative

Features

- Equipped with one or two auxiliary electrodes to ensure quick and reliable ignition
- Single-ended gas-filled glass bulb (HG-SG) with a quartz mercury vapour discharge tube
- Internally coated ovoid outer bulb, providing a cool, bluish white light with reasonable color qualities

Application

- All outdoor applications, factories, transport sector and industrial area lighting


Versions



HPL, 100W, E39

HPL-N

Dimensional drawing



Product	D (max)	C (max)
HPL-N 100W E39 HG 1SL/12	76 mm	188 mm

