



产品描述

HPL-N

标准高压汞灯

优点

- 初始投资低,经济实惠

特点

- 白色灯光 : 色温 4100K

应用

- 道路照明,室内外工业照明

安全提示

- For use with control gear designed for high-pressure mercury lamps
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

应用	
能效标签 (EEL)	B
控制调光	
可调光	否
基本信息	
LSF 2000 小时额定	99 %
操作位置	UNIVERSAL
灯具设计要求	
灯泡温度 (最高)	350 °C
照明科技	
颜色代码	542
颜色名称	冷 白色 (CW)
机械和壳体	
灯泡外观	涂层玻璃

应用

Order Code	Full Product Name	能耗 kWh/1000 h	汞 (Hg) 含量 (标称)
928051007391	HPL-N 80W/542 E27 1CT/24	88 kWh	14.0 mg
928052007391	HPL-N 125W/542 E27 1CT/24	137 kWh	19.0 mg
928053007492	HPL-N 250W/542 E40 1SL/12	275 kWh	38 mg
928053507493	HPL-N 400W/542 E40 1SL/6	440 kWh	72 mg

运营和电气 (1/2)

Order Code	Full Product Name	灯具电流 (EM) (标称)	电压 (最 高)	电压 (最 低)	电压 (标 称)
928051007391	HPL-N 80W/542 E27 1CT/24	0.8 A	125 V	105 V	115 V
928052007391	HPL-N 125W/542 E27 1CT/24	1.15 A	135 V	115 V	125 V

Order Code	Full Product Name	灯具电流 (EM) (标称)	电压 (最 高)	电压 (最 低)	电压 (标 称)
928053007492	HPL-N 250W/542 E40 1SL/12	2.1 A	145 V	125 V	135 V
928053507493	HPL-N 400W/542 E40 1SL/6	3.25 A	150 V	130 V	140 V

运营和电气 (2/2)

Order Code	Full Product Name	功率 (额定) (标称)
928051007391	HPL-N 80W/542 E27 1CT/24	80.0 W
928052007391	HPL-N 125W/542 E27 1CT/24	125.0 W

Order Code	Full Product Name	功率 (额定) (标称)
928053007492	HPL-N 250W/542 E40 1SL/12	250.0 W
928053507493	HPL-N 400W/542 E40 1SL/6	400.0 W

基本信息 (1/2)

Order Code	Full Product Name	底盖 (标称)	20% 故障条件下的使用寿命	50% 故障条件下的使用寿命	5% 故障条件下的使用寿命
928051007391	HPL-N 80W/542 E27 1CT/24	E27	12000 h	20000 h	6000 h
928052007391	HPL-N 125W/542 E27 1CT/24	E27	12000 h	20000 h	6000 h

Order Code	Full Product Name	底盖 (标称)	20% 故障条件下的使用寿命	50% 故障条件下的使用寿命	5% 故障条件下的使用寿命
928053007492	HPL-N 250W/542 E40 1SL/12	E40	10000 h	15000 h	5000 h
928053507493	HPL-N 400W/542 E40 1SL/6	E40	10000 h	15000 h	5000 h

基本信息 (2/2)

Order Code	Full Product Name	LSF 12000 小时额定	LSF 16000 小时额定	LSF 20000 小时额定	LSF 4000 小时额定	LSF 6000 小时额定	LSF 8000 小时额定
928051007391	HPL-N 80W/542 E27 1CT/24	80 %	68 %	50 %	98 %	95 %	92 %
928052007391	HPL-N 125W/542 E27 1CT/24	80 %	68 %	50 %	98 %	95 %	92 %
928053007492	HPL-N 250W/542 E40 1SL/12	65 %	45 %	28 %	97 %	92 %	83 %
928053507493	HPL-N 400W/542 E40 1SL/6	65 %	45 %	28 %	97 %	92 %	83 %

照明科技 (1/3)

		色度坐标	色度坐标	相关色温 (标	显色指数			色度坐标	色度坐标	相关色温 (标	显色指数
Order Code	Full Product Name	X (标称)	Y (标称)	称)	(标称)	Order Code	Full Product Name	X (标称)	Y (标称)	称)	(标称)
928051007391	HPL-N 80W/542 E27 1CT/24	370	366	4300 K	45	928053007492	HPL-N 250W/542 E40 1SL/12	381	383	4100 K	40
928052007391	HPL-N 125W/542 E27 1CT/24	374	373	4100 K	46	928053507493	HPL-N 400W/542 E40 1SL/6	384	384	3900 K	40

照明科技 (2/3)

		LLMF 12000	LLMF 16000	LLMF 2000	LLMF 20000	LLMF 4000	LLMF 6000	LLMF 8000	2000 小时下的 光通维持率 (最	2000 小时下的 光通维持率 (标
Order Code	Full Product Name	小时额定	小时额定	小时额定	小时额定	小时额定	小时额定	小时额定	低)	称)
928051007391	HPL-N 80W/542 E27 1CT/24	85 %	80 %	92 %	76 %	91 %	89 %	88 %	82 %	92 %
928052007391	HPL-N 125W/542 E27 1CT/24	85 %	80 %	92 %	76 %	91 %	89 %	88 %	82 %	92 %
928053007492	HPL-N 250W/542 E40 1SL/12	78 %	75 %	88 %	72 %	86 %	84 %	82 %	78 %	88 %
928053507493	HPL-N 400W/542 E40 1SL/6	78 %	75 %	88 %	72 %	86 %	84 %	82 %	78 %	88 %

照明科技 (3/3)

		5000 小时 下的光通维	5000 小时 下的光通维	光效 (额	光通量 (额			5000 小时 下的光通维	5000 小时 下的光通维	光效 (额	光通量 (额
Order Code	Full Product Name	持率 (最低)	持率 (标称)	定)(标称)	定)(标称)	Order Code	Full Product Name	持率 (最低)	持率 (标称)	定)(标称)	定)(标称)
928051007391	HPL-N 80W/542 E27 1CT/24	80 %	90 %	44.5 lm/W	3600 lm	928053007492	HPL-N 250W/542 E40 1SL/12	75 %	85 %	51 lm/W	12700 lm
928052007391	HPL-N 125W/542 E27 1CT/24	80 %	90 %	50 lm/W	6200 lm	928053507493	HPL-N 400W/542 E40 1SL/6	75 %	85 %	55 lm/W	22000 lm

机械和壳体

Order Code	Full Product Name	灯泡材料	灯泡外形	Order Code	Full Product Name	灯泡材料	灯泡外形
928051007391	HPL-N 80W/542 E27 1CT/24	软玻璃	BF70	928053007492	HPL-N 250W/542 E40 1SL/12	硬玻璃	ED90
928052007391	HPL-N 125W/542 E27 1CT/24	软玻璃	E75	928053507493	HPL-N 400W/542 E40 1SL/6	硬玻璃	ED120

