



# 產品說明

## HPI-T 複金屬燈

石英複金屬燈，透明外部燈泡

### 优点

- 高度安全，照明舒適，歷久如新
- 維護成本極低

### 特点

- 透明外管
- 獨特的 3 段技術，有效提升流明效率，亮度始終如一
- 產生自然色白光，光色穩定

### 应用

- 運動照明，建物和紀念碑泛光照明、區域照明 (如港口和建築工地) 等

### 安全提示

- Use only in totally enclosed luminaire, even during testing (IEC61167, IEC 62035, IEC60598)
- The luminaire must be able to contain hot lamp parts if the lamp ruptures
- For use with control gear designed for high-pressure mercury lamps
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.


# HPI-T 複金屬燈

## Versions




HPI-T 1000W E40

## 二维绘图



| Product                   | D (max) | O     | L      | C (max) |
|---------------------------|---------|-------|--------|---------|
| HPI-T 1000W/543 E40 1SL/4 | 66 mm   | 80 mm | 240 mm | 382 mm  |



| Product                        | D (max)  | O      | L      | C (max) |
|--------------------------------|----------|--------|--------|---------|
| HPI-T 2000W/542 E40 380V 1SL/4 | 101.5 mm | 120 mm | 267 mm | 430 mm  |
| HPI-T 2000W/646 E40 220V CRP/4 | 101.5 mm | 89 mm  | 290 mm | 430 mm  |

| 一般資訊  |          |
|-------|----------|
| 燈座基底  | E40      |
| 照明技術  |          |
| 色彩名稱  | 冷白光 (CW) |
| 控制與調光 |          |
| 可調光   | 否        |
| 機械與外罩 |          |
| 燈泡表層  | 透明       |

HPI-T 複金屬燈

一般資訊

| Order Code   | Full Product Name              | 操作位置 | Order Code   | Full Product Name              | 操作位置 |
|--------------|--------------------------------|------|--------------|--------------------------------|------|
| 928482600096 | HPI-T 1000W/543 E40 1SL/4      | P    | 928074209228 | HPI-T 2000W/542 E40 380V 1SL/4 | P20  |
| 928073609231 | HPI-T 2000W/646 E40 220V CRP/4 | P75  |              |                                |      |

照明技術

| Order Code   | Full Product Name              | 色度坐標 X (標稱) | 色度坐標 Y (Nom) | 相關色彩溫度 (規範) | 演色性指數 (CRI) | 光效 (額定) (標準) |
|--------------|--------------------------------|-------------|--------------|-------------|-------------|--------------|
| 928482600096 | HPI-T 1000W/543 E40 1SL/4      | 370         | 380          | 4300 K      | 57          | 83 lm/W      |
| 928073609231 | HPI-T 2000W/646 E40 220V CRP/4 | 375         | 385          | 4200 K      | 63          | 95 lm/W      |
| 928074209228 | HPI-T 2000W/542 E40 380V 1SL/4 | 387         | 403          | 3800 K      | 59          | 101 lm/W     |

運轉與電力

| Order Code   | Full Product Name              | 電壓 (標稱) | 耗電量     | Order Code   | Full Product Name              | 電壓 (標稱) | 耗電量     |
|--------------|--------------------------------|---------|---------|--------------|--------------------------------|---------|---------|
| 928482600096 | HPI-T 1000W/543 E40 1SL/4      | 130 V   | 990 W   | 928074209228 | HPI-T 2000W/542 E40 380V 1SL/4 | 232 V   | 1,980 W |
| 928073609231 | HPI-T 2000W/646 E40 220V CRP/4 | 130 V   | 1,980 W |              |                                |         |         |

機械與外罩

| Order Code   | Full Product Name              | 燈泡形狀 | Order Code   | Full Product Name              | 燈泡形狀 |
|--------------|--------------------------------|------|--------------|--------------------------------|------|
| 928482600096 | HPI-T 1000W/543 E40 1SL/4      | T65  | 928074209228 | HPI-T 2000W/542 E40 380V 1SL/4 | T100 |
| 928073609231 | HPI-T 2000W/646 E40 220V CRP/4 | T100 |              |                                |      |

認證與應用

| Order Code   | Full Product Name              | 能源消耗 kWh/<br>1000 h | 汞 (Hg) 含量 (標稱) | Order Code   | Full Product Name        | 能源消耗 kWh/<br>1000 h | 汞 (Hg) 含量 (標稱) |
|--------------|--------------------------------|---------------------|----------------|--------------|--------------------------|---------------------|----------------|
| 928482600096 | HPI-T 1000W/543 E40 1SL/4      | 1089 kWh            | 86 mg          | 928074209228 | HPI-T 2000W/542 E40 380V | 2178 kWh            | 256 mg         |
| 928073609231 | HPI-T 2000W/646 E40 220V CRP/4 | 2178 kWh            | 155 mg         |              | 1SL/4                    |                     |                |

