



Product Description

MASTER MHN-LA

Compact quartz metal halide lamps with double-pin

Benefits

- Allows compact and efficient luminaire systems with precision optics for good beam control and minimal spill light
- Allows compact and efficient luminaire systems with precision optics for good beam control and minimal spill light
- Good color rendering creates a pleasant ambience with high visual comfort for players and spectators
- Good colour rendering creates a pleasant ambience with high visual comfort for players and spectators
- Continuous spectral distribution offers options for semi-professional stadiums and for professional stadiums with regular TV coverage
- Continuous spectral distribution offers options for semi-professional stadiums and for professional stadiums with regular TV coverage

Features

- Compact source (Long Arc) with high luminous efficacy
- Compact source (Long Arc) with high luminous efficacy
- Double-pin concept results in long lifetime
- Double-pin concept results in long lifetime
- Natural white color appearance, high color rendering and good color stability
- Natural white colour appearance, high colour rendering and good colour stability
- Daylight color temperature eases transition from daylight to artificial lighting
- Daylight colour temperature eases transition from daylight to artificial lighting

Application

- Professional and semi-professional sports lighting and floodlighting
- Professional and semi-professional sports lighting and floodlighting

MASTER MHN-LA

Warnings and Safety


- Use only in totally enclosed luminaire, even during testing (IEC61167, IEC 62035, IEC60598)
- Use only in totally enclosed luminaire, even during testing (IEC61167, IEC 62035, IEC60598)
- The luminaire must be able to contain hot lamp parts if the lamp ruptures
- The luminaire must be able to contain hot lamp parts if the lamp ruptures
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Versions



LPPR MHN-LA 2000W

Dimensional drawing



Product	D (max)	O	X	A
MASTER MHN-LA 1000W/842 230V XWH	40 mm	40.5 mm	35 mm	286 mm
MASTER MHN-LA 1000W/956 230V XWH	40 mm	40.5 mm	35 mm	286 mm
MASTER MHN-LA 2000W/956 400V XWH	40 mm	108 mm	58 mm	353 mm

General Information	
Cap-Base	X528
Operating Position	P5
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Finish	Clear
Bulb Shape	TD40

Light Technical

MASTER MHN-LA

Order Code	Full Product Name	Chromaticity	Chromaticity	Color Designation	Correlated Color	Color rendering	Luminous Efficacy
		Coordinate X (Nom)	Coordinate Y (Nom)		Temperature (Nom)	index (CRI)	(rated) (Nom)
928072505130	MASTER MHN-LA 2000W/956 400V XWH	330	339	Daylight	5600 K	82	93 lm/W
928072205130	MASTER MHN-LA 1000W/956 230V XWH	337	331	Daylight	5600 K	80	86.0 lm/W
928073005130	MASTER MHN-LA 1000W/842 230V XWH	366	370	Cool White (CW)	4200 K	70	92.00 lm/W

Operating and Electrical

Order Code	Full Product Name	Voltage (Nom)	Power Consumption	Order Code	Full Product Name	Voltage (Nom)	Power Consumption
928072505130	MASTER MHN-LA 2000W/956 400V XWH	225 V	2,040.0 W	928073005130	MASTER MHN-LA 1000W/842 230V XWH	125 V	1,040.0 W
928072205130	MASTER MHN-LA 1000W/956 230V XWH	125 V	1,040.0 W				

Approval and Application

Order Code	Full Product Name	Energy Consumption	Mercury (Hg)	Order Code	Full Product Name	Energy Consumption	Mercury (Hg)
		kWh/1000 h	Content (Nom)			kWh/1000 h	Content (Nom)
928072505130	MASTER MHN-LA 2000W/956 400V XWH	2244 kWh	140 mg	928073005130	MASTER MHN-LA 1000W/842 230V XWH	1144 kWh	112 mg
928072205130	MASTER MHN-LA 1000W/956 230V XWH	1144 kWh	95 mg				

