




# PrimaVision Mini (20W, 35W & 50W) for CDM – Miniature size to enhance creativity

## PrimaVision Mini for CDM

Miniature HID electronic gear for PGJ5 CDM lamps – freeing up the boundaries of creativity and innovation in luminaire design

### Benefits

- Miniaturization enables stylish luminaire design and retrofit halogen replacement
- Optimal lamp performance thanks to minimal lamp power tolerance
- Easy luminaire design-in

### Features

- Loop Through feature (in independent version)
- Smallest gear and highest wattage in miniature size
- Minimal lamp power spread
- Microprocessor-controlled
- Lamp end-of-life detection
- High Tambient and Tcase temperatures
- Long lifetime of 40,000 hours

### Application

- 20/35/50 W accent and decorative lighting for shops, public spaces, lobbies and offices
- Suitable for indoor use only




# PrimaVision Mini for CDM

## Versions



GPPR IPV5CDMM 0011

## Dimensional drawing




| Product                                | D1     | C1      | A1       | A2       | A3       | B1      |
|----------------------------------------|--------|---------|----------|----------|----------|---------|
| HID-PV m 20 /I CDM<br>220-240V 50/60Hz | 4.8 mm | 34.0 mm | 234.7 mm | 225.1 mm | 202.0 mm | 49.4 mm |
| HID-PV m 35/I CDM<br>220-240V 50/60Hz  | 4.8 mm | 34.0 mm | 234.7 mm | 225.1 mm | 202.0 mm | 49.4 mm |

| Product                                    | D1     | C1      | A1      | A2      | B1      |
|--------------------------------------------|--------|---------|---------|---------|---------|
| HID-PV m 20 /S CDM 220-240V<br>50/60Hz     | 4.2 mm | 30.2 mm | 97.3 mm | 88.3 mm | 43.3 mm |
| HID-PV m 35 /S CDM 220-240V<br>50/60Hz     | 4.2 mm | 30.2 mm | 97.3 mm | 88.3 mm | 43.3 mm |
| HID-PV m 50 /S CDM HPF 220-240V<br>50/60Hz | 4.2 mm | 30.2 mm | 97.3 mm | 88.3 mm | 43.3 mm |

| Product                                 | D1     | C1      | A1       | A2       | B1      |
|-----------------------------------------|--------|---------|----------|----------|---------|
| HID-PV m PGJ5 20 /I CDM LPF<br>220-240V | 4.2 mm | 30.0 mm | 190.0 mm | 154.0 mm | 43.3 mm |

# PrimaVision Mini for CDM

## Dimensional drawing



| Product                             | D1     | C1      | A1      | A2      | B1      |
|-------------------------------------|--------|---------|---------|---------|---------|
| HID-PV m PGJ5 20/S CDM HPF 220-240V | 4.2 mm | 30.0 mm | 97.3 mm | 88.3 mm | 43.3 mm |

| Operating and Electrical |              |
|--------------------------|--------------|
| Input Frequency          | 50 to 60 Hz  |
| Input Voltage            | 220 to 240 V |
| Line Frequency           | 50 to 60 Hz  |

## Operating and Electrical

| Order Code   | Full Product Name                    | Number of Products on MCB (16A Type B) (Nom) |
|--------------|--------------------------------------|----------------------------------------------|
| 913700601666 | HID-PV m PGJ5 20 /I CDM LPF 220-240V | 48                                           |
| 913700646266 | HID-PV m 20 /I CDM 220-240V 50/60Hz  | 24                                           |
| 913700653566 | HID-PV m 35/I CDM 220-240V 50/60Hz   | 24                                           |
| 913700656766 | HID-PV m PGJ5 20/S CDM HPF 220-240V  | 24                                           |

| Order Code   | Full Product Name                       | Number of Products on MCB (16A Type B) (Nom) |
|--------------|-----------------------------------------|----------------------------------------------|
| 913700665966 | HID-PV m 50 /S CDM HPF 220-240V 50/60Hz | 24                                           |
| 913700696066 | HID-PV m 20 /S CDM 220-240V 50/60Hz     | 32                                           |
| 913700696166 | HID-PV m 35 /S CDM 220-240V 50/60Hz     | 24                                           |

## Mechanical and Housing

| Order Code   | Full Product Name                    | Housing     |
|--------------|--------------------------------------|-------------|
| 913700601666 | HID-PV m PGJ5 20 /I CDM LPF 220-240V | /I          |
| 913700646266 | HID-PV m 20 /I CDM 220-240V 50/60Hz  | Independent |
| 913700653566 | HID-PV m 35/I CDM 220-240V 50/60Hz   | Independent |
| 913700656766 | HID-PV m PGJ5 20/S CDM HPF 220-240V  | Standard    |

| Order Code   | Full Product Name                       | Housing |
|--------------|-----------------------------------------|---------|
| 913700665966 | HID-PV m 50 /S CDM HPF 220-240V 50/60Hz | /S      |
| 913700696066 | HID-PV m 20 /S CDM 220-240V 50/60Hz     | /S      |
| 913700696166 | HID-PV m 35 /S CDM 220-240V 50/60Hz     | /S      |

