



Powerful, ultra-slim circular lamps

T5 Circular

Philips T5 Circular lamps are ultra-slim with improved color rendering, higher efficacy, and longer life. T5 HO circular lamps offer extraordinary light output.

Benefits

- Slim profile lamp and ballast enables fixtures to be 45% smaller than T9 Circline systems.
- Long Life to assist with lowering your maintenance costs and reducing waste.
- Operates on Programmed Start Electronic Ballasts.

Features

- Design flexibility.
- Improved optical control.
- Fixtures can be 45% smaller than standard T9 circline systems.
- Dimmable for additional energy savings.
- Energy efficient.
- Less material means less waste.
- Longer life.
- Available in 22 and 40 Watts with 3000, 3500, 4100 color temperatures. T5 HO Circular Lamps are available in 55 Watt with 3000, 3500 and 4100 color temperatures.

Application

- Ideal for offices and commercial establishments where smaller, more appealing fixture designs are required


T5 Circular

Versions



C-T5 2GX13

Dimensional drawing



Product	D (max)	D (min)	E (min)	E (max)	I (min)	I (max)
TL5C 40W/835	18 mm	14 mm	293 mm	305 mm	260 mm	272 mm

