



Latina – simple and effective

Latina FBH024

Latina is a recessed downlight for compact fluorescent PL-C lamps, with spring fasteners for easy and quick installation. Square and round models are available. Latina comes in ready-to-install kit versions, including lamps and pre-connected separate gearbox. The round models are available in glass versions (frosted glass or clear decorative glass) or in open versions. For the open versions, the same glass designs are available as accessories (to be ordered separately). The square versions are always with glass.

Benefits

- Easy to install and connect: all-in-one kit

Features

- Square and round models
- Frosted or clear decorative glass

Application

- Shops
- Offices

Specifications

Type	FBH024
Light source	Compact fluorescent: <ul style="list-style-type: none">- 2 x MASTER PL-C 2 Pin / G24d-2 / 18 W- 2 x MASTER PL-C 2 Pin / G24d-3 / 26 W- 2 x MASTER PL-C 4 Pin / G24q-2 / 18 W- 2 x MASTER PL-C 4 Pin / G24q-3 / 26 W
Lamp included	Yes (K or lamp color 830 or 840)
Lamp position	Horizontal

Gear	Electro magnetic (low loss), 230 or 240 V / 50 Hz: <ul style="list-style-type: none">- Inductive (I)- Inductive, parallel compensated (IC) Electronic, 220 - 240 V / 50 - 60 Hz: <ul style="list-style-type: none">- High Frequency (HF)
Material	Body and gear box: metal Reflector: high-gloss anodized metal
Installation	Fixation by means of spring fasteners

Latina FBH024


Maintenance	Direct lamp access or after removing the front glass
Accessory (for open versions)	Frosted glass cover, clear decorative glass cover

Versions



Latina FBH024 recessed downlight with fixed clear decorative glass cover

Dimensional drawing



Latina FBH020

Accessories

Frosted glass
Ordercode 88531299



Recessed glass, structured
Ordercode 88532999



Approval and Application

Ingress protection code	IP20
-------------------------	------

Operating and Electrical

Input Voltage	230 to 240
---------------	------------

General Information

CE mark	CE mark
Color	White
Protection class IEC	Safety class I (I)
Compensation circuit	-
Flammability mark	F
Gear	HF
Glow-wire test	960/5
Kombipack	Lamp(s) included
Lamp family code	PL-C/4P
Number of light sources	2

General Information

order code	Decorative accessories	Lamp power	Product Family Code
88500899	RG	18	FBH024
88502299	RG	18	FBH024
88504699	RG	26	FBH024
88506099	RG	26	FBH024
88503999	FRG	18	FBH024
88505399	FRG	26	FBH024
88507799	FRG	26	FBH024
88509199	No	18	FBH024
88510799	No	26	FBH024
88511499	No	26	FBH024

