



FBH059

FBH059

The FBH and FBS family of recessed downlights come complete with a highly efficient frosted aluminum reflector and polished strip faceted upper surface. They are specially designed for compact fluorescent 10W/13W/18W/26W lamps. A standard ballast is integrated with the luminaires. A clear glass option is available upon request.

Features

- Adjustable swing out metal clip integrates easily various ceiling systems.
- Maintenance is simplified with direct lamp access from below
- Front Glass version is available

Application

- Offices
- Retail
- Hospitality

Versions



Approval and Application

| | |
|-------------------------|------|
| Ingress protection code | IP20 |
|-------------------------|------|

Operating and Electrical

| | |
|---------------|-------|
| Input Voltage | 220 V |
|---------------|-------|

General Information

| | |
|----------------------|-----------|
| Compensation circuit | Inductive |
|----------------------|-----------|

| | |
|-----------------|----|
| Country version | NO |
|-----------------|----|

| | |
|------|------|
| Gear | CONV |
|------|------|

| | |
|------------------|---------|
| Lamp family code | PL-C/2P |
|------------------|---------|

| | |
|-------------------------|-------|
| Number of light sources | 2 pcs |
|-------------------------|-------|

Mechanical and Housing

| | |
|-------|-------|
| Color | White |
|-------|-------|

General Information

| Order Code | Full Product Name | Lamp power |
|--------------|--------------------------|------------|
| 910401945280 | FBH059 2xPL-C/2P18W I WH | 18 W |
| 910401945380 | FBH059 2xPL-C/2P26W I WH | 26 W |

