



Compact and robust design

D'ECO Light Collection FBH311/312

The D'ECO Light Collection range offers distinctive design and a wide variety of models and formats. With a compact and discreet design it maintains the same consistent look throughout the range and offers several optical system options, from glass to anti-glare shades. Easy to install and highly flexible, it can be adjusted to accommodate different-sized lamps with the same luminaire.

Benefits

- Easy to install
- Wide variety of optical systems
- Fine frame
- High performance

Features

- Aluminum-plate body in white color
- Aluminum reflector with metallic finish
- Round or square frame
- Recessed or surface-mounted
- Options with flat frosted glass, recessed frosted glass or recessed glass with 4 or 9-wing shade
- For the MHN / CDM-TD metal-halide lamp version there is also a chassis with equipment (ballast)

Application

- Ideal for general lighting in shops, hotels and offices

Specifications

D'ECO Light Collection FBH311/312

Type	FBH311
	FBH312
Light source	2 x 18 W, 2 x 26 W / PL-C 4P
Mains voltage	Electronic 220 V / 60-50 Hz: (EB)
Optical cover	Frosted recessed glass (FBH311)
	Recessed glass with 4-wing shade (FBH312)

Materials and finishing	Aluminum-plate body
	Aluminum reflector and shade with metallic finish
Installation	Recessed in the ceiling, in niches of 195 x 195 mm

Versions



General Information

Lamp family code	PL-C/4P
Number of light sources	2 pcs

Mechanical and Housing

Color	White
--------------	-------

General Information

Order Code	Full Product Name	Optical cover/lens		Gear	Lamp power
		type			
919406004811	FBH311 2XPL-C/4P26W GF WH	Glass frosted	-	-	26 W
919406004881	FBH312 2XPL-C/4P26W WH	-	-	-	26 W

Order Code	Full Product Name	Optical cover/lens		Gear	Lamp power
		type			
919406004891	FBH312 2XPL-C/4P18W/840 EB WH	-	-	EB	18 W

