



# Europa 2 – efficient and easy

## Europa 2

Europa 2 is a fixed recessed downlight for compact fluorescent PL-C lamps with highly efficient optics and automatic fixing clips for quick and easy installation. These downlights are available in two formats and can be fitted with a prismatic light control panel, opal cover, clear front panel or glare-control louver. Europa 2 is available in a ready-to-install kit version.

### Benefits

- No hassle – ready-to-install kit with a flexible gear connection, thereby saving on installation time
- ‘Green’ promise – high-frequency gear, energy-saving PL-C lamps and less material used in production and packaging
- Modern rim design and pendant glass accessories

### Features

- 1- and 2-CFL lamp versions and different lamp colors
- Emergency lighting: 1- and 3-hour versions available
- Cover accessories and decorative pendant glasses
- Highly efficient aluminum-covered reflector (aluminum layer is damped on)
- Tilttable lamp holders ensure easy lamp replacement
- Flexible connection between gear and luminaire

### Application

- Offices – corridors, entrances, toilet areas
- Retail – general lighting

### Specifications

Type	FBS120 (compact version)	Light source	Compact fluorescent:
	FBS122 (mini version)		- 1 x or 2 x MASTER PL-C 4 Pin / G24q-1 / 13 W

## Europa 2

	- 1 x or 2 x MASTER PL-C 4 Pin / G24q-2 / 18 W
	- 1 x or 2 x MASTER PL-C 4 Pin / G24q-3 / 26 W
<b>Lamp included</b>	No (for emergency lighting versions) Yes (K or lamp color 830 or 840)
<b>Lamp position</b>	Horizontal
<b>Gear</b>	Electronic, 220 - 240 V / 50 - 60 Hz: - High Frequency (HF)
<b>Optical cover</b>	Opal cover (O)
	Protection glass (PG)
	Prismatic cover, clear (P)
	Louver (L)
<b>Connection</b>	Cable Wieland, 3 pole (CW3)
	Cable Wieland, 2 pole (CW2)
	Cable with CEE 7 plug (CCE)
	Push-in connector (PI)

<b>Option</b>	Emergency lighting: - 1 hour (EL1), 3 hours (EL3)
<b>Material</b>	Housing: plastic, injection moulded
	Reflector: plastic, injection moulded with high efficient reflective layer
<b>Installation</b>	Fixation by means of spring fasteners
<b>Accessory</b>	Protection cover IP44 (PG/G), opal cover IP44 (O), louver (L), prismatic cover (P)
<b>Remarks</b>	Ready to install kit versions available (KIT)
<b>Main applications</b>	Office, retail, hospitality

## Accessories



Opal diffuser

Ordercode 08936000



Ordercode 08937700



Ordercode 66251000

