



Europa 2 – efficient and easy

Europa 2

Europa 2 is a fixed recessed downlight for compact fluorescent PL-C lamps with highly efficient optics and automatic fixing clips for quick and easy installation. These downlights are available in two formats and can be fitted with a prismatic light control panel, opal cover, clear front panel or glare-control louver. Europa 2 is available in a ready-to-install kit version.

Benefits

- No hassle – ready-to-install kit with a flexible gear connection, thereby saving on installation time
- ‘Green’ promise – high-frequency gear, energy-saving PL-C lamps and less material used in production and packaging
- Modern rim design and pendant glass accessories

Features

- 1- and 2-CFL lamp versions and different lamp colors
- Emergency lighting: 1- and 3-hour versions available
- Cover accessories and decorative pendant glasses
- Highly efficient aluminum-covered reflector (aluminum layer is damped on)
- Tilttable lamp holders ensure easy lamp replacement
- Flexible connection between gear and luminaire

Application

- Offices – corridors, entrances, toilet areas
- Retail – general lighting

Specifications

Type	FBS120 (compact version)	Light source	Compact fluorescent:
	FBS122 (mini version)		- 1 x or 2 x MASTER PL-C 4 Pin / G24q-1 / 13 W

Europa 2

	- 1 x or 2 x MASTER PL-C 4 Pin / G24q-2 / 18 W
	- 1 x or 2 x MASTER PL-C 4 Pin / G24q-3 / 26 W
Lamp included	No (for emergency lighting versions) Yes (K or lamp color 830 or 840)
Lamp position	Horizontal
Gear	Electronic, 220 - 240 V / 50 - 60 Hz: - High Frequency (HF)
Optical cover	Opal cover (O)
	Protection glass (PG)
	Prismatic cover, clear (P)
	Louver (L)
Connection	Cable Wieland, 3 pole (CW3)
	Cable Wieland, 2 pole (CW2)
	Cable with CEE 7 plug (CCE)
	Push-in connector (PI)

Option	Emergency lighting: - 1 hour (EL1), 3 hours (EL3)
Material	Housing: plastic, injection moulded
	Reflector: plastic, injection moulded with high efficient reflective layer
Installation	Fixation by means of spring fasteners
Accessory	Protection cover IP44 (PG/G), opal cover IP44 (O), louver (L), prismatic cover (P)
Remarks	Ready to install kit versions available (KIT)
Main applications	Office, retail, hospitality

Accessories

Opal diffuser

Ordercode 910500451914



Protection glass

Ordercode 910500451915



Ordercode 910502424915



Ordercode 910502428615

