



F/MBS145

FBH/FBS145 C

Professional standard recessed downlights with a 145mm internal diameter. Complete with a very efficient highly polished reflector in silver aluminium finish. Suitable for incandescent, halogen, compact fluorescent and high intensity discharge lamps.

Features

- Modular concept - same cut out diameter allows a consistent appearance and interchangeable accessories and components
- Adjustable swing out metal clip integrates easily into various ceiling systems
- Maintenance is simplified with direct lamp access from below
- Employs highly efficient reflector with a polished upper part to increase reflection while the frosted lower part contributes to better glare control
- Die cast aluminium housing creates a compact and sturdy architecture to interface with different accessories

Application

- Mixed use shopping centres
- Corridors
- Department stores - general lighting
- High-end fashion shops and boutiques
- Restaurants, cafeterias and hotels
- Museum display, public buildings and waiting areas
- Transport buildings e.g. airport terminals and interchanges
- Small offices and conference rooms

FBH/FBS145 C

Versions



FBS145 downlight

Approval and Application

Ingress protection code	IP20
-------------------------	------

Operating and Electrical

Maximum lamp power	-
--------------------	---

General Information

Cap-Base	-
Compensation circuit	Inductive
Country version	NO
Optical cover/lens type	-
Gear	CONV
Lamp family code	PL-C/2P
Lamp power	13 W

Mechanical and Housing

Color	White
-------	-------

General Information

Order Code	Full Product Name	Number of light sources
910403630216	FBH145 C 1xPL-C/2P13W I WH	1 pc
910403630219	FBH145 C 2xPL-C/2P13W I WH	2 pcs

