



Compact and robust design

D'ECO Light Collection FBS320/321/323/331

The D'ECO Light Collection range offers distinctive design and a wide variety of models and formats. With a compact and discreet design, it maintains the same consistent look throughout the range and offers several optical system options, from glass to anti-glare shades. Easy to install and highly flexible, it can be adjusted to accommodate different-sized lamps with the same luminaire.

Benefits

- Easy to install
- Wide variety of optical systems
- Fine frame
- High performance

Features

- Aluminum-plate body in white color
- Aluminum reflector with metallic finish
- Round or square frame
- Recessed or surface-mounted
- Options with flat frosted glass, recessed frosted glass or recessed glass with 4 or 9-wing shade
- For the MHN / CDM-TD metal-halide lamp version there is also a chassis with equipment (ballast)

Application

- Ideal for general lighting in shops, hotels and offices

Specifications

D'ECO Light Collection FBS320/321/323/331

Type	FBS320
	FBS321
	FBS323
	FBS331
Light source	1 x 18 W, 1 x 26 W, 2 x 18 W, 2 x 26 W / PL-C 2P
	1 x 18 W, 1 x 26 W, 2 x 18 W, 2 x 26 W / PL-C 4P
	2 x 32 W / PL-T 4P
Mains voltage	Electromagnetic (high power factor): 220 V / 60 Hz
	Electronic 220 V / 60-50 Hz: (EB)

Optical cover	Frosted flat glass (GF)
	Recessed frosted glass (FBS321, FBS331)
	Recessed glass with 9-wing shade (FBS323)
Materials and finishing	Aluminum-plate body
	Aluminum reflector and shades with metallic finish
Installation	Recessed in the ceiling, in niches of Ø 200 mm

Versions



Mechanical and Housing

Color	White
--------------	-------

Operating and Electrical

Order Code	Full Product Name	Input Voltage
919406003801	FBS320 1XPL-C/2P18W/840 220V-60HZ GF WH	220 V
919406003851	FBS320 1XPL-C/4P18W/840 EB GF WH	-
919406003861	FBS320 1XPL-C/4P26W/840 EB GF WH	-
919406003871	FBS320 2XPL-C/4P26W GF WH	220 V
919406003881	FBS320 2XPL-C/4P18W/840 EB GF WH	220 V
919406003891	FBS320 2XPL-C/4P26W/840 EB GF WH	220 V
919406003901	FBS321 1XPL-C/2P18W/840 220V-60HZ GF WH	220 V
919406003911	FBS321 1XPL-C/2P26W/840 220V-60HZ GF WH	220 V

Order Code	Full Product Name	Input Voltage
919406003921	FBS321 2XPL-C/2P18W/840 220V-60HZ GF WH	220 V
919406003931	FBS321 2XPL-C/2P26W/840 220V-60HZ GF WH	220 V
919406003971	FBS321 2XPL-C/4P26W GF WH	220 V
919406003981	FBS321 2XPL-C/4P18W/840 EB GF WH	220 V
919406003991	FBS321 2XPL-C/4P26W/840 EB GF WH	220 V
919406004251	FBS323 2xPL-C/4P32W/840 EB WH	220 V
919406004351	FBS331 2XPL-T/4P32W/840 EB GF WH	-

General Information

Order Code	Full Product Name	Optical cover/lens type	Gear	Lamp family code	Lamp power	Number of light sources
919406003801	FBS320 1XPL-C/2P18W/840 220V-60HZ GF WH	Glass frosted	-	PL-C/2P	18 W	1 pc
919406003851	FBS320 1XPL-C/4P18W/840 EB GF WH	Glass frosted	EB	PL-C/4P	18 W	1 pc
919406003861	FBS320 1XPL-C/4P26W/840 EB GF WH	Glass frosted	EB	PL-C/4P	26 W	1 pc
919406003871	FBS320 2XPL-C/4P26W GF WH	Glass frosted	-	PL-C/4P	26 W	2 pcs
919406003881	FBS320 2XPL-C/4P18W/840 EB GF WH	Glass frosted	EB	PL-C/4P	18 W	2 pcs
919406003891	FBS320 2XPL-C/4P26W/840 EB GF WH	Glass frosted	EB	PL-C/4P	26 W	2 pcs
919406003901	FBS321 1XPL-C/2P18W/840 220V-60HZ GF WH	Glass frosted	-	PL-C/2P	18 W	1 pc
919406003911	FBS321 1XPL-C/2P26W/840 220V-60HZ GF WH	Glass frosted	-	PL-C/2P	26 W	1 pc
919406003921	FBS321 2XPL-C/2P18W/840 220V-60HZ GF WH	Glass frosted	-	PL-C/2P	18 W	2 pcs

D'ECO Light Collection FBS320/321/323/331

Order Code	Full Product Name	Optical cover/lens type	Gear	Lamp family code	Lamp power	Number of light sources
919406003931	FBS321 2XPL-C/2P26W/840 220V-60HZ GF WH	Glass frosted	-	PL-C/2P	26 W	2 pcs
919406003971	FBS321 2XPL-C/4P26W GF WH	Glass frosted	-	PL-C/4P	26 W	2 pcs
919406003981	FBS321 2XPL-C/4P18W/840 EB GF WH	Glass frosted	EB	PL-C/4P	18 W	2 pcs
919406003991	FBS321 2XPL-C/4P26W/840 EB GF WH	Glass frosted	EB	PL-C/4P	26 W	2 pcs
919406004251	FBS323 2xPL-C/4P32W/840 EB WH	-	EB	PL-T/4P	32 W	2 pcs
919406004351	FBS331 2XPL-T/4P32W/840 EB GF WH	Glass frosted	EB	PL-T/4P	32 W	2 pcs

