



# Flexible system design and brilliant optical control

## FastFlex LED module

Philips FastFlex LED module offers high-quality, reliable, easy-to-use outdoor LED illumination for roads and urban street lighting. The system offers outstanding optical control and flexible system design.

### Benefits

- Perfectly match each project's needs
- Easy factory assembly and reliable lifetime performance
- Low cost of thermal management

### Features


- Modular approach to luminaire design; choice of 4 optical distributions
- LUXEON T LEDs in CCT 4000 K, CRI 70 or 80
- Patented interface between lens, module and mounting surface
- High Tcase 75 °C
- Lean supply chain

### Application


- Road lighting
- Flood and Area lighting
- Urban street lighting

# FastFlex LED module


## Versions




## Dimensional drawing



**Product**  
FastFlex lens 2x8/III-X




**Product**  
FastFlex lens 2x8/II-X



**Product**  
FastFlex lens 2x8/V

FastFlex LED module

Dimensional drawing



Product
FastFlex lens 2x8/IV-X

