



# ET-Standard Transformer

## ET-S transformer

High-frequency electronic transformer (60, 105 and 150 W versions available), operation with 12 V halogen lamps

### 优点

- High efficiency compared with magnetic transformer
- Easy luminaire design-in with EMI compliance
- Dimmable with Philips-approved leading- and trailing-edge dimmers

### 特点

- 30,000 hours lifetime
- EMI-compliant
- Screw connector
- CE, SELV approval
- Safe operation with overload, short circuit and overheating protection

### 应用


- Indoor residential: living rooms, decorative and accent lighting
- Professional applications: reception areas, offices, retail spaces and exhibition rooms

ET-S transformer

Versions



二维绘图



| Product              | D1     | C1      | B2      | A1       | A2       | B1      |
|----------------------|--------|---------|---------|----------|----------|---------|
| ET-S 15 LED 220-240V | 3.4 mm | 29.0 mm | 23.4 in | 115.0 mm | 105.0 mm | 45.0 mm |

