



Product Description

Primaline Halogen Transformers

High-Frequency electronic transformer for operation with 12V halogen lamps, available in 70W, 105W and 150W versions

Benefits

- Low power losses, resulting in increased energy saving
- Constant light output in the case of under-voltage and a full service life in the case of over-voltage
- ENEC, SELV, CE and EMC-compliant

Features

- Very compact and lightweight design; fits in small downlight halogen applications
- Three levels of protection: over-voltage, over-temperature and short circuit
- Long lifetime: 50,000 hours
- Dimming possible with Philips-approved Leading and Trailing Edge dimmers
- Possible to connect two lamps for 70 and 105 W, and three lamps for 150 W

Application

- Indoor residential use including living rooms and decorative and accent lighting
- Professional applications including retail, offices, conference rooms and exhibitions

Warnings and Safety

- Transformer is not suitable for DC operation

Primaline Halogen Transformers

Versions



GPPR_ET-P_105_70-Product photo

Dimensional drawing

| Product | C1 | A1 | B1 |
|-------------------------------|-------|--------|-------|
| Primaline 70 230-240V 50/60Hz | 33 mm | 110 mm | 45 mm |

