



Product Description

HalogenA PAR20

Mains-voltage 63 mm diameter reflector lamp

Benefits

- Bright, sparkling halogen light
- Convenient halogen solutions that fit in standard, existing luminaires
- Retrofit halogen replacement for R60/R63 incandescent reflector lamps

Features

- Hard-glass halogen burner optically positioned in a parabolic, aluminium-coated pressed-glass reflector (PAR) with new optical pressing design
- Excellent colour rendering
- White, crisp sparkling halogen light
- Long life (2.5 times the lifetime of a normal incandescent lamp)
- Spot versions have slightly stippled front glass to emphasise the sparkling reflector
- Flood versions have a faceted front glass to prevent glare and ensure a homogeneous beam distribution
- Front glass protects the lamp for safety and prevents touching and dust deposits

Application

- Typically used for accent and display lighting in shops, especially for premium goods
- Also used as accent and task lighting in the home

HalogenA PAR20

Dimensional drawing

Product	D	C
HalogenA PAR20 50W E27 230V 25D 1CT/15	65 mm	105 mm
HalogenA PAR20 50W E27 230V 25D 1CT/15	65 mm	105 mm
HalogenA PAR20 50W E27 230V 25D 1CT/15	64 mm	105 mm
HalogenA PAR20 50W E27 230V 25D 1CT/15	64 mm	105 mm

PAR20 50W E27 230V 25D

