



Product Description

HalogenA PAR30S

Mains-voltage 97 mm diameter reflector lamp

Benefits

- Bright, sparkling halogen light
- Convenient halogen solutions that fit in standard, existing luminaires

Features

- Hard-glass halogen burner (linear filament) optically positioned in a parabolic, aluminium-coated pressed-glass reflector (PAR)
- Natural colour rendering
- Sparkling, crisp white halogen light
- Good luminous efficacy
- Long life (two to two and a half times the lifetime of a normal incandescent lamp)
- Spot versions have slightly stippled front glass to emphasise the sparkling reflector
- Flood versions have a faceted front glass to prevent glare and ensure a homogeneous beam distribution
- Front glass protects the lamp for safety and prevents touching and dust deposits

Application

- Typically used for accent and display lighting in shops, especially for premium goods
- Also used as general lighting in hotels, theaters and lobby areas

HalogenA PAR30S


Versions




Dimensional drawing

D

Product	D (max)	C (max)
HalogenA Par30s 75W E27 230V 25D 1CT/15	96 mm	99 mm




Accent Diagrams



LDAC_HPAR30S_75W_30D-Accent diagram

Beam Diagrams



LDBE_HPAR30S_75W_30D-Beam diagram

