



Product Description

HalogenA PAR30S

Mains-voltage 97 mm diameter reflector lamp

Benefits

- Bright, sparkling halogen light to put your objects in the spotlight
- Bright, sparkling halogen light
- Fully dimmable, from 0 to 100%, to meet different brightness requirements
- Convenient halogen solutions that fit in standard, existing luminaires
- Low replacement costs due to long lifetime

Features

- Superior quality of light with excellent color rendering (Ra=100)
- Hard-glass halogen burner (linear filament) optically positioned in a parabolic, aluminium-coated pressed-glass reflector (PAR)
- Mains-voltage lamp, no transformer needed
- Natural colour rendering
- Universal burning position
- Sparkling, crisp white halogen light
- Instant start
- Good luminous efficacy
- Long life (two to two and a half times the lifetime of a normal incandescent lamp)
- Spot versions have slightly stippled front glass to emphasise the sparkling reflector
- Flood versions have a faceted front glass to prevent glare and ensure a homogeneous beam distribution
- Front glass protects the lamp for safety and prevents touching and dust deposits

Application

- Spot accent lighting to create the right ambiance in hotels, restaurants and shops
- Typically used for accent and display lighting in shops, especially for premium goods
- Also used as general lighting in hotels, theaters and lobby areas