



Spot of crisp white light from modern-looking aluminum reflector

Aluline 111 燈泡

Low-voltage halogen burner in decorative aluminum reflector equipped with antiglare cap. Ideal solution for high-end modern luminaires, putting your objects in the spotlight. Aluminum coating prevents heat in the backlight.

优点

- Bright, sparkling halogen light to put your objects in the spotlight
- Fully dimmable, from 0 to 100%, to meet different brightness requirements
- Low replacement costs due to long lifetime

特点

- Superior quality of light with excellent color rendering (Ra=100)
- Low-pressure technology with UV-block glass allows use in luminaires without front glass
- Aluminum coating
- Lifetime: 3000 hours
- Instant start

应用

- Spot accent lighting to create the right ambiance in hotels, restaurants and shops

Aluline 111 燈泡


Versions




二维绘图



Product	D (max)	C (max)	C1 (max)
Aluline 111 50W G53 12V 24D 1CT/6	111 mm	67 mm	51 mm




Accent Diagrams



LDAC_HALUACN_50W_24D-Accent diagram

Aluline 111 燈泡

Beam Diagrams



LDBE_HALUACN_50W_24D-Beam diagram

