



Product Description

Brilliantline Dichroic

Low-voltage, xenon gas-filled halogen burner with axial filament optically positioned in a glass reflector

Benefits

- Cool beam as a large part of the heat generated is transmitted backwards through the back glass

Features

- High-intensity beam with a clearly defined beam spread
- Reflector has a light-reflecting, light-transmitting hard dichroic coating
- Constant high quality and aesthetics maintained over lifetime
- Wide range of 35mm and 50 mm types
- UV-Block front glass
- Excellent colour rendering
- GU5.3 or GU4 base for extra retention in luminaire

Application


- Ideally suited for accent, task and decorative lighting in shops, stores, hotels, restaurants etc.

Brilliantline Dichroic

Versions



Dimensional drawing



Product	D (max)	C (max)
Brilliantline Dichroic 20W GU4 12V 30D 1CT/10X5F	35 mm	40 mm

