



Product Description

Capsuleline

Single-ended low-voltage halogen capsule giving crisp white halogen light

Benefits

- Low-pressure technology allows use in luminaires without front glass

Features

- Sturdy, low-pressure lamps with UV-Block glass (IEC 357)
- Gas-filled (≤ 2.5 bar) lamps can be used in luminaires without a front glass in accordance with IEC 598
- Axial filament for higher light output in combination with luminaires and a uniform beam
- Excellent colour rendering
- Universal burning position


Application

- Task lighting and decorative applications in homes, shops, hotels and restaurants

Versions



Dimensional drawing



Product	D (max)	L	C (max)
Capsuleline 50W GY6.35 12V CL 4000h 1CT/10X10F	12 mm	30 mm	44 mm

