



The new halogen mains-voltage capsule. Compact shape, crisp white light

Halogen Clickline G9

Ideal solution for small decorative luminaires. UV-block glass and safety fuse allow usage without cover glass. The compact Clickline gives crisp white light over a long lifetime.

Benefits

- Bright, sparkling halogen light to create the right atmosphere
- Fully dimmable, from 0 to 100%, to meet different brightness requirements
- Lower replacement cost due to longer burning hours

Features


- Superior quality of light with excellent color rendering (Ra=100)
- Mains-voltage lamp, no transformer needed
- Compact size, easy to fit in the luminaire
- Universal burning position
- Instant start

Application

- General lighting in shops, restaurants, hotels, galleries, exhibitions and museums. Ideal for use in small, decorative luminaires

Halogen Clickline G9

Dimensional drawing



General Information	
Cap-Base	G9
Rated Lifetime (Hours)	2,000 hour(s)
Switching Cycle	8,000
Nominal lifetime	2,000 hour(s)
Operating Position	UNIVERSAL
Light Technical	
Correlated Color Temperature (Nom)	2800 K
Color rendering index (CRI)	100
Operating and Electrical	
Warm-up time to 60% light	instant full light s
Voltage (Nom)	230 V
Starting Time (Nom)	0.0 s
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Finish	Clear
Bulb Shape	T13

Product	D (max)	L	C (max)
Halogen MV Caps 28W G9 230V CL 1BC/10	13 mm	21.7 mm	45 mm
Halogen MV Caps 44.0W G9 230V 1PF/10 SRT	13 mm	21.7 mm	45 mm
Halogen MV Click 19.0W G9 230V CL 1CT	13 mm	21.7 mm	45 mm
Halogen MV Click 28W G9 230V CL 1CT	13 mm	21.7 mm	45 mm
Halogen MV Click 29.0W G9 230V CL 1CT	13 mm	21.7 mm	45 mm
Halogen MV Click 44.0W G9 230V CL 1CT	13 mm	21.7 mm	45 mm

Light Technical

Order Code	Full Product Name	Chromaticity	Chromaticity	Luminous	Luminous Flux
		Coordinate X (Nom)	Coordinate Y (Nom)	Efficacy (rated) (Nom)	
925640644201	Halogen MV Click 29.0W G9 230V CL 1CT	-	-	12.1 lm/W	370 lm
925640644202	Halogen MV Caps 28W G9 230V CL 1BC/10	-	-	12.1 lm/W	370 lm
925640644205	Halogen MV Click 28W G9 230V CL 1CT	0.452	0.409	12.1 lm/W	350 lm
925640844201	Halogen MV Click 44.0W G9 230V CL 1CT	-	-	15 lm/W	630 lm
925640844214	Halogen MV Caps 44.0W G9 230V 1PF/10 SRT	-	-	15 lm/W	630 lm
925697744209	Halogen MV Click 19.0W G9 230V CL 1CT	-	-	11.1 lm/W	204 lm

Operating and Electrical

Order Code	Full Product Name	Lamp Current (Nom)	Power Consumption
925640644201	Halogen MV Click 29.0W G9 230V CL 1CT	0.12 A	28.0 W
925640644202	Halogen MV Caps 28W G9 230V CL 1BC/10	0.12 A	28.0 W
925640644205	Halogen MV Click 28W G9 230V CL 1CT	0.12 A	29 W

Order Code	Full Product Name	Lamp Current (Nom)	Power Consumption
925640844201	Halogen MV Click 44.0W G9 230V CL 1CT	0.18 A	42.0 W
925640844214	Halogen MV Caps 44.0W G9 230V 1PF/10 SRT	0.18 A	42.0 W
925697744209	Halogen MV Click 19.0W G9 230V CL 1CT	0.08 A	18 W

Approval and Application

Halogen Clickline G9

Order Code	Full Product Name	Energy Consumption kWh/1000 h
925640644201	Halogen MV Click 29.0W G9 230V CL 1CT	28 kWh
925640644202	Halogen MV Caps 28W G9 230V CL 1BC/10	28 kWh
925640644205	Halogen MV Click 28W G9 230V CL 1CT	29 kWh
925640844201	Halogen MV Click 44.0W G9 230V CL 1CT	42 kWh

Order Code	Full Product Name	Energy Consumption kWh/1000 h
925640844214	Halogen MV Caps 44.0W G9 230V 1PF/10 SRT	42 kWh
925697744209	Halogen MV Click 19.0W G9 230V CL 1CT	18 kWh

